



P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	PRODUCTION RELEASE	19JAN2022	SCB	PS



NOTES:



1 MATERIALS & FINISH
 HOUSING : PA66, UL94 V0, COLOR - LIGHT GREEN
 CONTACT : BRASS, TIN PLATED

2. ELECTRICAL

RATED VOLTAGE	: 300V
RATED CURRENT	: 16A (UG B)
	: 10A (UG D)
INSULATION RESISTANCE	: >2000 M Ohm (500V DC)


3. OPERATING TEMPERATURE RANGE : -40°C TO +105°C

$\triangle_4$ TOLERANCE NOT CUMULATIVE




RECOMMENDED PCB LAYOUT

82.88	16	1-2385009-6
77.80	15	1-2385009-5
72.72	14	1-2385009-4
67.64	13	1-2385009-3
62.56	12	1-2385009-2
57.48	11	1-2385009-1
52.40	10	1-2385009-0
47.32	9	2385009-9
42.24	8	2385009-8
37.16	7	2385009-7
32.08	6	2385009-6
27.00	5	2385009-5
21.92	4	2385009-4
16.84	3	2385009-3
11.76	2	2385009-2
DIM A	NO. OF POS	TE PN



2385009-3 AS SHOWN

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 13 JAN 2022 SHRICHARANA B CHK 13 JAN 2022 SUBHASREE S APVD 13 JAN 2022 PRASHANTH S PRODUCT SPEC 108-32299 APPLICATION SPEC 114-32242 WEIGHT -		DIM A NO. OF PCB TE PIN	
DIMENSIONS: mm 		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± 1 PLC ± 2 PLC ± 3 PLC ± 4 PLC ± ANGLES ±		TE Connectivity 	
MATERIAL 		FINISH 		NAME TERMINAL BLOCK, 180 DEG HEADER, PITCH 5.08mm, TAIL LENGTH 4.5mm -	
		CUSTOMER DRAWING		SIZE A3	
		CAGE CODE 00779		DRAWING NO C-2385009	
		RESTRICTED TO -		SCALE 5:1	
		SHEET 1 OF 1		REV A	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[2385009-8](#)