





P	LTR	DESCRIPTION	DATE	DWN	APVD
	Z1	NOTE 5 ADDED TO DRAWING	06APR2021	KJK	PS

SEC. A-A



- NOTES:
- 1 LCP, BLACK, UL94V-0
 - 2 NORYL SE-1 RED COLOUR
 - 3 NON CUMULATIVE TOLERANCE
 - 4 PERMITTED FLASH 0.25mm MAX
 - 5 OPTIONAL RIBS EQUALLY SPACED



OBSOLETE	4	1-280359-0	7.62	10.6	12.2	1
	2	1-280358-0	2.54	5.6	7.1	
	22	280364	53.34	56.4	57.9	
	15	280363	35.56	38.6	40.1	
	12	280514	27.94	31.0	32.5	
	10	280362	22.86	25.9	27.4	
	9	280512	20.32	23.3	24.9	
	8	280361	17.78	20.8	22.3	
	6	280360	12.70	15.7	17.3	
	4	280359	7.62	10.6	12.2	
	2	280358	2.54	5.6	7.1	2
	NUM OF POS.	PART NUMBER	DIM "A"	DIM "B"	DIM "C"	

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm

MATERIAL
-

TOLERANCES UNLESS OTHERWISE SPECIFIED:
±0.3

0 PLC
1 PLC
2 PLC
3 PLC
4 PLC
ANGLES
FINISH

±
±
±
±
±
±2°
-

DWN
KARTHIK J K
CHK
SHARATH S
APVD
PRASHANTH S
PRODUCT SPEC
108-20025
APPLICATION SPEC
114-20004
WEIGHT
-

20MAR2018
15OCT2018
15OCT2018

CUSTOMER DRAWING

TE Connectivity

NAME
AMPMODU II REC. HSG
SINGLE ROW, CRIMP ON- SNAP IN
-

SIZE
A3

CAGE CODE
00779

DRAWING NO
C-280358

RESTRICTED TO
-

SCALE
5:1

SHEET
1 OF 1

REV
Z1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[280514](#)