




© 2021 TE Connectivity. All Rights Reserved.

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	T	REDRAWN. PLASTIC SUPPLIER CHANGED	28MAY2021	SB	KJK



PARTIAL SEC. Z-Z

- NOTES:
- 1 FINISH: 3-5 µm TIN OVER MIN 1.27 µm NICKEL
 - 2 FINISH: DUPLEX PLATED MIN 0.38 µm GOLD IN CONTACT AREA AND 2.5 µm TIN IN SOLDER AREA. OVER MIN 1.27 µm NICKEL.
 - 3 FINISH: DUPLEX PLATED MIN 0.76 µm GOLD IN CONTACT AREA AND 2.5 µm TIN IN SOLDER AREA. OVER MIN 1.27 µm NICKEL.
 - 4 MATERIALS:
 - HOUSINGS: FLAME RETARDANT THERMOPLASTIC. UL94V0. COLOR BLACK.
 - TIN AND GOLD PLATED CONTACTS: BRASS
 - 5 OBSOLETE
 - 6 RECOMMENDED PCB HOLES DIA: 1.1⁺⁰_{-0.2}; 0.75 MIN. ADMITTED FOR 2 POS. ONLY

58.5	53.34	5	280383-3	280383-2	280383-1	22
40.7	35.56	5	280382-3	280382-2	280382-1	15
33.1	27.94	5	280523-3	280523-2	280523-1	12
28.0	22.86		280381-3	280381-2	280381-1	10
25.4	20.32	5	280511-3	5 280511-2	280511-1	9
22.9	17.78		280380-3	280380-2	280380-1	8
17.8	12.70		280379-3	280379-2	280379-1	6
12.7	7.62		280378-3	280378-2	280378-1	4
7.7	2.54		280377-3	280377-2	280377-1	2
D	B	3	PART NUMBER	2 PART NUMBER	1 PART NUMBER	NO. POS.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN G. CAMPIA 12FEB1990			
CHK -		NAME AMPMODU II SHROUDED HEADER SINGLE ROW, RIGHT ANGLE POST			
APVD -		PRODUCT SPEC 108-20025		SIZE A3	
MATERIAL 4		APPLICATION SPEC -		CAGE CODE 00779	
FINISH -		WEIGHT -		DRAWING NO C-280377	
		CUSTOMER DRAWING		RESTRICTED TO	
		SCALE 4:1		SHEET 1 OF 1	
				REV T	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[280381-3](#)