

1471-9 (3/13)

D

C

B

A

Printed on 18 Oct 2021 15:05 (India Standard Time) from TEL54782

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

TE CONNECTIVITY

ALL RIGHTS RESERVED.

2MM - HSD - D - HT - - - -

PRODUCT SERIES

2MM AMPMODU 2mm series

GENDER / TYPE

HSD Shrouded headers for detent latch

NUMBER OF ROWS

D Double row

NUMBER OF PINS PER ROW

XX 02 through 16,20,22,25 (enter two digits)

ORIENTATION & TERMINATION

HT Horizontal through hole

SMART PART NUMBER

PACKAGING

TB Tube without cap

TBP Tube with cap

TRP Tape and reel with cap

BX Box

PLATING

T Tin

F 0.1µm Gold (Gold flash)

M 0.38µm Gold

H 0.76µm Gold

TAIL LENGTH

01 2.2 mm

02 2.8 mm

03 3.4 mm

SMART PN EXAMPLES :

1. AMPMODU 2MM, SHROUDED HEADER STD VERSION, DOUBLE ROW , 02 POSITION PER ROW , RIGHT ANGLE MOUNT, 2.2MM SOLDER TAIL LENGTH, TIN PLATING, TUBE W/O CAP
2MM-HSD-D02-HT-01-T-TB

2. AMPMODU 2MM, SHROUDED HEADER STD VERSION, DOUBLE ROW , 25 POSITION PER ROW , RIGHT ANGLE MOUNT, 3.4MM SOLDER TAIL LENGTH, 0.76µm GOLD PLATING, BOX PACKAGING
2MM-HSD-D25-HT-03-H-BX

THIS PRINT IS
PRELIMINARY
UNQUALIFIED PRODUCT
CONTACT PRODUCT ENGINEERING
BEFORE USING THIS PRINT

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: mm

MATERIAL SEE NOTES

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ±
1 PLC ±0.1
2 PLC ±0.05
3 PLC ±
4 PLC ±
ANGLES ±2°
FINISH

SEE NOTES

DWN 11FEB2016 RAKSHITH NAYAK
CHK 01APR2016 KARTHIK J K
APVD 01APR2016 PRASHANTH S

PRODUCT SPEC 108-64040
APPLICATION SPEC 114-64040
WEIGHT -

CUSTOMER DRAWING

TE Connectivity

NAME AMPMODU 2mm SHROUDED HEADER, DUAL ROW , RIGHT ANGLE

SIZE A2 CAGE CODE 00779 DRAWING NO C=2823351 RESTRICTED TO -

SCALE 1:1 SHEET 3 OF 3 REV A3

D

C

B

A

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1-2823354-6](#)