






REVISIONS					
P.	LTR.	DESCRIPTION	DATE	DWN.	APVD.
	B	REV PER ECO 19-010704	7-15-19	CT	JS

- 1 MATERIAL: STAINLESS STEEL (303)
- 2 FINISH: PASSIVATED
- 3 ANNULAR RING PLATED AROUND GUIDE PIN MOUNTING HOLE ON TOP AND BOTTOM SIDE OF BOARD
- 4 NO SECONDARY KEYING FEATURE
- 5 DENOTES RELATIONSHIP BETWEEN PRIMARY AND SECONDARY KEYING FEATURES.
- 6 PIN CAN BE ROTATED IN INCREMENTS OF 45° CREATING 8 POSSIBLE KEYING VARIATIONS FOR EACH PART NUMBER








2828454-2	24	7.25	5.7	1.50	315°	1-2828999-8
2828454-3	24	7.25	5.7	1.50	270°	1-2828999-7
2828454-4	24	7.25	5.7	1.50	225°	1-2828999-6
2828454-5	24	7.25	5.7	1.50	180°	1-2828999-5
2828454-4	24	7.25	5.7	1.50	135°	1-2828999-4
2828454-3	24	7.25	5.7	1.50	90°	1-2828999-3
2828454-2	24	7.25	5.7	1.50	45°	1-2828999-2
2828454-1	24	7.25	5.7	2.00	4	1-2828999-1
2828454-2	24	7.25	2.6	1.50	315°	2828999-8
2828454-3	24	7.25	2.6	1.50	270°	2828999-7
2828454-4	24	7.25	2.6	1.50	225°	2828999-6
2828454-5	24	7.25	2.6	1.50	180°	2828999-5
2828454-4	24	7.25	2.6	1.50	135°	2828999-4
2828454-3	24	7.25	2.6	1.50	90°	2828999-3
2828454-2	24	7.25	2.6	1.50	45°	2828999-2
2828454-1	24	7.25	2.6	2.00	4	2828999-1
MATES WITH	DIM L	DIM K	DIM J	DIM T	DIM S	PART NUMBER



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN A. TSANG CHK K. MILLER	04APR2016 06APR2016	TE Connectivity	
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ±.2 1 PLC ±0.2 2 PLC ±0.08 3 PLC ±0.001 4 PLC ±0.0001 ANGLES ±1°		NAME GUIDE PIN, CLOCKABLE KEYED, 64 POSN, CUSTOM APERTURE STD FOOTPRINT, BP, MULTIGIG	
MATERIAL		FINISH		SIZE A1	
CUSTOMER DRAWING		WEIGHT 5.80g		CAGE CODE -	
SCALE 8:1		SHEET 1 OF 2		REV B	

REVISIONS					
P.	LTR.	DESCRIPTION	DATE	DWN.	APVD.
	-	SEE SHEET 1	-	-	-



THIS PRINT IS
PRELIMINARY
UNQUALIFIED PRODUCT
CONTACT PRODUCT ENGINEERING
BEFORE USING THIS PRINT

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN A. TSANG 04APR2016	TE Connectivity	
DIMENSIONS:		CHK K. MILLER 06APR2016		
mm		APVD -	NAME GUIDE PIN, CLOCKABLE KEYED, 64 POSN, CUSTOM APERTURE STD FOOTPRINT, BP, MULTIGIG	
		PRODUCT SPEC	SIZE A1	
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APPLICATION SPEC	CAGE CODE -	
0 PLC ±.2 1 PLC ±0.2 2 PLC ±0.08 3 PLC ±0.001 4 PLC ±0.0001		FINISH -	DRAWING NO C=2828999	
MATERIAL		WEIGHT 5.80g	RESTRICTED TO -	
		CUSTOMER DRAWING	SCALE 8:1	
			SHEET 2 OF 2	
			REV B	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1-2828999-2](#)