




4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

2008

© COPYRIGHT 2008

ALL RIGHTS RESERVED.

LOC

DIST

REVISIONS

P

LTR

DESCRIPTION

DATE

DWN

APVD

SEE SHEET 1

NUMERO DI VIE	CONFIGURAZIONE (Vista connettore dall'alto)	VERSIONE PEZZI IN VASSOIO	PART REV.	VERSIONE PEZZI SCIOITI	PART REV	POSIZIONE AGGANCIO (LATO POSTERIORE)	POSIZIONE POLARIZZAZIONE (LATO POSTERIORE) (SE PRESENTE)	L +0.2 -0.3 (mm)	NOTE MARCHIATURA CON BANDA COLORATA
NO OF POS	CONFIGURATION (View from top side)	TRAY PACKAGING VERSION		LOOSE PIECES PACKAGING VERSION		LOCKING POSITION (Back side)	POSITION FOR POLARIZATION ON BACK SIDE (IF PRESENT)		NOTE STRIP COLOUR
2		0-293491-2	D	-	-	1-2	1S-2D	9.9	-
		1-293491-2	D	-	-	1-2	1S	9.9	-
		2-293491-2	D	-	-	1-2	-	9.9	-
3		0-293491-3	D	-	-	2-3	2S	14.9	-
3		1-293491-3	D	-	-	1-2	1S-2D	14.9	BLACK
4		0-293491-4	D	-	-	1-2, 3-4	1S,2D,3S	19.9	-
4		1-293491-4	1	-	-	1-2, 3-4	1S,2D	19.9	-
8		0-293491-8	D	-	-	1-2, 7-8	2D,3S,6D,7S	39.9	-

SCALE 2:1
VISTA LATO ALTO
(TOP SIDE VIEW)

POSIZIONE BANDA COLORATA
(COLOR STRIP AREA)

AGGANCIO POSTERIORE
(REAR LOCKING LANCE)
BETWEEN WAYS 2-3

POLARIZATION RIB
POSITION 2S AS SHOWN

NUMERO DELLA VIA
(WAY NUMBERING)

SCALE 2:1

CODIFICHE ASPORTABILI
(REMOVABLE CODIFICATION)

NOTE/NOTES:

1

NUMERI DI IDENTIFICAZIONE CAVITA'.
(CIRCUIT IDENTIFICATION)

2

MARCHIO DI FABBRICA (LIBERA POSIZIONE).
(TRADE MARK LOGO FREE POSITION)

3

L'AGGANCIO PER LINGUETTA E' POSIZIONATO SOLO NELLA CAVITA' N 1 °VEDI ANCHE NOTA 5
(RETENTION TOOTH IT IS LOCATED ON THE CAVITY N.1 SEE ALSO NOTE 5)

4

DIVENTA 6.5 PER LA CAVITA' N. 1 SUI CONNETTORI
(BECOMES 6.5. FOR THE CAVITY N.1)

5

GEOMETRIA ALTERNATIVA E OPZIONALE DEL DENTINO DI AGGANCIO
(ALTERNATIVE AND OPTIONAL SHAPE FOR RETENTION TOOTH)

6

STATO DI FORNITURA: CONFEZIONAMENTO IN "VASSOI + SCATOLA"
(PACKAGING: "ON TRAY PLUS CARTON BOX")

7

PRELIMINARY- PART NOT YEST RELEASED FOR PRODUCTION

8

SLIDE PROFILE (WEDGE SHAPE SLOT) ON THE AREA ABOVE THE LOCKING LANCE GEOMERTY TO FACILITATE UN-CHAINING PROCESS.

9

DIFFERENT CODING RIB GEOMETRY AT BOTH END.
WIDTH OF CODING RIB REDUCED TO 1.1 mm FOR ALL REAR LOCKING VERSIONS

PEZZO FORNITO AGGANCIATO IN STICK
(CONNECTORS STACKED IN STRIP)

FROM 11.4 TO 12.4
PASSO (PITCH)

CONNETTORE CHIUSO AGGRAFFATO
(TERMINATED CONNEGTOR)

24.5 MAX.

7.8 +0.1 -0.2

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ±

1 PLC ±

2 PLC ±

3 PLC ±

4 PLC ±

ANGLES ±

FINISH

±0.3

±0° 30'

SEE TABLE

DWN
C.CORDOLA 02DEC2008

CHK
G.TURCO 02DEC2008

APVD
-

PRODUCT SPEC
108-20065-1
108-20065-2

APPLICATION SPEC
114-20016
114-20016-1

WEIGHT
-

CUSTOMER DRAWING

NAME
MONO SHAPE MK I TAB
SPECIAL 2-8 POS REAR LOCKING
-

SIZE
A3

CAGE CODE
00779

DRAWING NO
C-293491

RESTRICTED TO
-

SCALE
2:1

SHEET
2 OF 3

REV
D5

1470-19 (3/11)

PA GF, UL-VO GWEPT 750 °C NO FLAME, NATURAL

NO OF POS	CONFIGURATION (View from top side)	TRAY PACKAGING VERSION	PART REV	LOOSE PIECES PACKAGING VERSION	PART REV	LOCKING POSITION (Back side)	POSITION FOR POLARIZATION ON BACK SIDE (IF PRESENT)	L +0.2 -0.3 (mm)	NOTE STRIP COLOUR
2		2297762-2	D	-	-	1-2	1S-2D	9.9	-
		1-2297762-2	1	-	-	1-2	1S	9.9	-
3		2297762-3	1	-	-	1-2	1S-2D	14.9	-
3		1-2297762-3	D	-	-	2-3	1D-2S-3D	14.9	-
4		2297762-4	D	-	-	1-2, 3-4	2D-3S-4D	19.9	-
5		2297762-5	1	-	-	2-3, 4-5	2S-4S	24.9	-
8		2297762-8	1	-	-	TBD	TBD	39.9	-

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm

MATERIAL
SEE TABLE

TOLERANCES UNLESS
OTHERWISE SPECIFIED:

0 PLC ±

1 PLC ±

2 PLC ±

3 PLC ±

4 PLC ±

ANGLES ±0° 30'

FINISH SEE TABLE

DWN
C.CORDOLA
02DEC2008

CHK
G.TURCO
02DEC2008

APVD
-

PRODUCT SPEC

APPLICATION SPEC
-

WEIGHT
-

CUSTOMER DRAW ING

TE Connectivity

NAME
MONO SHAPE MK I TAB
SPECIAL 2-8 POS REAR LOCKING
-

SIZE
A 3

CAGE CODE
00779

DRAWING NO
C-293491

RESTRICTED TO
-

SCALE
2:1

SHEET
3 OF 3

REV
D5

1470-19 (3/11)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[293491-2](#)