


REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	D2	REV PER ECN-22-150900	27APR2022	RK	CSD



AMP WIRE RANGE	 E13288 Listed
4/0 AWG SOLID OR STRANDED	4/0 AWG STRANDED

 LR7189 Certified
4/0 AWG SOLID OR STRANDED

- 1 STAMP AMP 4/0W* 200 APPROX AS SHOWN
- 2 COPPER PER ASTM B-152, ANNEALED
- 3 TIN PLATE 0.00254 [.000100] MIN PER ASTM B-545
- 4 MAX RECOMMENDED OPERATING TEMP 170°C
- 5 WIRE CROSS SECTIONAL AREA RANGE:
96.3-117.0mm² [190,000-231,000] CIR MILS
STRANDED OR SOLID


322228

B

A

322228

PART NO.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN DK SCHRUM 10/5/93	 TE Connectivity			
DIMENSIONS: MM [INCHES]		CHK AJ KAUFMAN 10/6/93				
		APVD JL MECKLEY 10/6/93	NAME TERMINAL, RING TONGUE, SOLISTRAND			
		PRODUCT SPEC —	APPLICATION SPEC —			
MATERIAL — 2		FINISH — 3	SIZE A2	CAGE CODE 00779	DRAWING NO C-322228	RESTRICTED TO —
CUSTOMER DRAWING			SCALE 2:1	SHEET 1 OF 1	REV D2	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[322228](#)