

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	T	PRODUCTION ISSUE	29JAN2019	PNT	MT





TABLE OF DIMENSIONS

PART NUMBER	H & J		K		P	R	S	T	HW & JW	KW
	Min	Max	Min	Max	±10%	±10%	±10%	±10%	±20%	±20%
	a	b	a	b	b	b	b	b	b	b
322A112	13.2 [.52]	5.8 [.23]	6.6 [.26]	3.0 [.12]	52.3 [2.06]	26.2 [1.03]	19.3 [.76]	N/A	1.52 [.06]	1.02 [.04]
322A123	26.9 [1.06]	12.4 [.49]	6.6 [.26]	3.0 [.12]	83.3 [3.28]	41.7 [1.64]	27.2 [1.07]	10.7 [.42]	2.54 [.10]	1.02 [.04]
322A134	26.9 [1.06]	12.7 [.50]	13.2 [.52]	5.8 [.23]	107.7 [4.24]	53.8 [2.12]	38.6 [1.52]	20.3 [.80]	2.54 [.10]	1.52 [.06]
322A148	55.6 [2.19]	25.4 [1.00]	13.2 [.52]	5.8 [.23]	180.6 [7.11]	90.4 [3.56]	57.4 [2.26]	25.4 [1.00]	4.57 [.18]	1.52 [.06]
322A158	55.6 [2.19]	25.4 [1.00]	26.9 [1.06]	12.4 [.49]	222.3 [8.75]	111.3 [4.38]	77.7 [3.06]	38.1 [1.50]	4.57 [.18]	2.54 [.10]

RELEASED FOR PUBLICATION

ALL RIGHTS RESERVED.

THIS DRAWING IS UNPUBLISHED.

© COPYRIGHT - TE Connectivity Ltd.

DIMENSIONS: mm [INCHES]	DWN	29JAN2019	MATERIAL	SEE SHEET 2		FINISH	-			
	CHK	29JAN2019	 TE Connectivity Ltd.							
TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD	29JAN2019								
0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± - 4 PLC ± - ANGLES ± -	PRODUCT SPEC	-								
	APPLICATION SPEC	-	NAME	TRANSITION, 90 DEG. SIDE BREAKOUT						
	WEIGHT	-	SIZE	A4	CAGE CODE	00779	DRAWING NO	C-322A112-XX-0THRU158-XX-0	RESTRICTED TO	-
CUSTOMER DRAWING			SCALE	DNS		SHEET	1 OF 2		REV	T

COMPATABILITY CHART				
MATERIAL DASH NO.	MATERIAL DESCRIPTION	RT SPEC	COATING SLASH NO.	COATING S NO.
-3	Polyolefin, Semi-rigid	RT-301	/42;/86;/180	S1017;S1048;S1030
-4	Polyolefin, Flexible	RT-1304	/42;/86;/180	S1017;S1048;S1030
-12	Fluoroelastomer, Flexible	RT-1312	N/A	N/A
-25	Elastomer, Fluid Resistant	RW-2070	/42;/86;/225	S1017;S1048;S1206
-100	Polyolefin, Semi-Flexible ZEROHAL	RW-2082	/86;/180	S1048;S1030

Diagram illustrating the breakdown of a part number into its components:

- Base part number**: 322A1XX
- Material dash number** (See Compatibility Chart): -XX
- Modification number**: -XX
- Adhesive slash number** (If necessary, see Compatibility Chart): /XX
- Color designator**: -0

1. Dimensions appearing in table are as follows:
 - a - As Supplied
 - b - After Unrestricted Recovery
2. Coating is optional. As supplied dimensions appearing in table are for uncoated parts. When coating is added, entry diameters will be reduced by 1.5mm[.06] max.
3. Molding ports are optional. When -00 modification number is specified molding ports will be located as shown. On size 322A112 the vent port will be eliminated.

1469-35 (1/15)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[322A123-12-0](#)