


REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	N3	REVISED PER ECN-22-150900	27APR2022	RK	CSD

AMP
WIRE RANGE

1/0 AWG
STRANDED



- 1 BODY MATERIAL THK 1.778±0.051[.070±.002]
- 2 FOR Ø14.732[Ø.580] MAX WIRE INS.
- 3 STAMP AMP 1/0 W* APPROX AS SHOWN.

50	LOOSE PC	324057
QTY	PACKAGE TYPE	PART NO

AMP INCORPORATED CUSTOMER SERVICE SYSTEMS			MAX RECOMMENDED OPERATING TEMPERATURE: 105°C[221°F]		THIS DRAWING IS A CONTROLLED DOCUMENT.				TE Connectivity				
FOR ADDITIONAL PRODUCT INFORMATION OR COPIES OF DRAWINGS AND TECHNICAL DOCUMENTS		PRODUCT INFORMATION CENTER 1-800-522-6752		VOLTAGE RATING: -		DIMENSIONS: mm [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED:		DWN S.S. GOULDEN 6-21-93			
FOR APPLICATION TOOLING INFORMATION		TOOLING ASSISTANCE CENTER 1-800-722-1111		CIRCULAR MIL AREA: 42.4-60.6mm² [83,700-119,500] STRANDED				0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± 0.127[.005] 4 PLC ± - ANGLES ± -		CHK R. HERSEY 6-21-93			
FOR ORDER ENTRY		1-800-526-5142		THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.				MATERIAL BODY: COPPER PER ASTM B-152 INSULATION: NYLON ASTM D4066 TYPE 1		FINISH BODY: TIN PLATE PER ASTM B545 INSULATION: COLOR-BLUE		APVD B. BARE 6-21-93	
						PRODUCT SPEC -		APPLICATION SPEC -		NAME TERMINAL, RING TONGUE, TERMINYL WIRE SIZE: 1/0 AWG -			
						WEIGHT -		CUSTOMER DRAWING		SIZE A3		CAGE CODE 00779	
								SCALE NTS		SHEET 1 OF 1		REV N3	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[324057](#)