





- 1 FOR 1.27 [.050] TO 2.08 [.082] WIRE INSULATION DIA
- 2 TONGUE MATERIAL THK: 0.46±0.05 [.018±.002]
- 3 APPLIES FROM THE METAL EDGE OF THE BARREL TO THE CENTER OF THE STUD
- 4 NOTE DELETED

100	LOOSE PC, BOX	BODY & SLEEVE: COPPER (ASTM-B152) TIN PL (ASTM-B545) INSULATION: NYLON COLOR: YELLOW (ASTM-D4066) TYPE 1	8-324075-1
4000	324075 ON TAPE		2-324075-1
1	WIRE TERMINAL		324075
QTY	DESCRIPTION	MATERIAL & FINISH	PART NO

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN RAGHAVENDRA 27AUG09	TE Connectivity				
		CHK JEFF RUTH 27AUG09					
DIMENSIONS: mm [INCHES]	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD TOM MICHIELUTTI 27AUG09	NAME WIRE TERMINAL PIDG – RING TONGUE WIRE SIZE: 26–22				
	0 PLC ± – 1 PLC ± – 2 PLC ± – 3 PLC ± 0.20 [.008] 4 PLC ± – ANGLES ± 5°	PRODUCT SPEC —					
MATERIAL	FINISH	APPLICATION SPEC —	SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO	
SEE TABLE	SEE TABLE	WEIGHT —	A3	00779	C–324075	—	
CUSTOMER DRAWING					SCALE 10:1	SHEET 1 OF 1	REV G3

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[2-324075-1](#)