





REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	H2	REVISED PER ECN-22-156403	06JUN2022	RK	CSD

AMP WIRE RANGE	 E13288 Listed	 LR7189 Certified
16-14 AWG SOLID OR STRANDED IR: STRANDED	16-14 AWG STRANDED	16-14 AWG SOLID OR STRANDED IR: STRANDED



-  STAMP "AMP - SEE TABLE" APPROX AS SHOWN.
-  WIRE INSULATION DIA: SEE TABLE.
-  BODY MATERIAL THK: .787±.051[.031±.002].
-  BODY: TIN PLATE .00254[.000100] MIN EXT THK PER ASTM B545.
-  SLEEVE: TIN PLATE .00254[.000100] MIN EXT THK PER ASTM B545.
-  BODY & SLEEVE- CU PER ASTM B152
INSULATION - NYLON PER ASTM D4066
-  APPLIES FROM EDGE OF METAL WIRE BARREL TO CENTER OF STUD HOLE.
-  MEETS MS25036-155, CLASS 1.
-  MEETS M7928/1-46, CLASS 1.
-  MEETS M7928/1-55, CLASS 1.
-  UL LISTED
-  CSA CERTIFIED




STYLE A



STYLE B
INSULATION RESTRICTING

	500	LOOSE PIECE	14*	1.981[.078]-3.302[.130]	14	GREEN	B			 2-328976-2
	500	LOOSE PIECE	16*	1.600[.063]-3.302[.130]	16	BLUE	B			 2-328976-1
	500	LOOSE PIECE	16-14*	2.667[.105]-3.810[.150]	16-14	--	A			 328976
QTY	PACKAGE TYPE	STAMPING	WIRE INSUL DIA	WIRE SIZE	STRIPE COLOR	STYLE	BODY FINISH	SLEEVE FINISH	PART NO	

CUSTOMER SERVICE SYSTEMS		MAX RECOMMENDED OPERATING TEMPERATURE: 105°C[221°F] MAX	THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN JR RUTH 13JAN10	 TE Connectivity				
FOR ADDITIONAL PRODUCT INFORMATION OR COPIES OF DRAWINGS AND TECHNICAL DOCUMENTS	PRODUCT INFORMATION CENTER 1-800-522-6752	VOLTAGE RATING: 300 VOLT MAX	DIMENSIONS: mm[INCHES]	TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± 0.127(.005) 4 PLC ± - ± - ANGLES ± -	CHK T MICHELUTTI 13JAN10					
FOR APPLICATION	TOOLING ASSISTANCE CENTER	CIRCULAR MIL AREA: 1.04-2.62mm²[2,050-5,180] STRANDED OR SOLID		FINISH  	APVD T MICHELUTTI 13JAN10	NAME TERMINAL, RING TONGUE, PIDG, WIRE SIZE: 16-14 AWG, PIDG IR 16 &14 AWG				
TOOLING INFORMATION	1-800-722-1111		MATERIAL 	INSULATION: COLOR-BLUE	PRODUCT SPEC UL 486A-B 	SIZE A2	CAGE CODE 00779	DRAWING NO C-328976	RESTRICTED TO -	
FOR ORDER ENTRY	1-800-526-5142				114-2157	WEIGHT -	SCALE 5:1	SHEET 1 OF 1	REV H2	
CUSTOMER DRAWING										

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[2-328976-1](#) [2-328976-2](#)