





LOC	DIST	REVISIONS			
		LTR	DESCRIPTION	DATE	APVD
H	-	E1	REVISED PER ECO-11-005294	30APR11	HMR



- NOTES:
- 1. WIRE RANGE 24-20 AWG
 - 2. INSULATION RANGE Ø .50- .060 (1,27-1,52 mm)
 - 3 FOR APPLICATOR USE ONLY
 - 4 FOR HANDTOOL USE ONLY
 - 5. FOR APPLICABLE CONNECTOR HOUSINGS SEE C-338095.



4 3	750	Pre-Tin	COSI-contact	Phosphorbronze	1-0338097-1
	15000	Pre-Tin	COSI-contact	Phosphorbronze	0-0338097-1
	Pcs/reel	Finish	Description	Material	Partnumber

ANCES UNLESS USE SPECIFIED: ± 0.2 ± 0.1 ± 0.05 ± 0.01 ± - ± -	DWN	TE TE Connectivity									
	CHK										
	H.v.Delft										
	APVD	-	NAME								
	PRODUCT SPEC		MICRO-MATCH COSI CONTACT								
	108-19052		20-24 AWG								
	APPLICATION SPEC	SIZE CAGE CODE DRAWING NO A3 00779 ©- 338097									
114-19051											
WEIGHT											
-											
tinplated	CUSTOMER DRAWING			SCALE	10:1	SHEET	1	OF	1	REV	E1

DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:	
	0 PLC	±	0,2
	1 PLC	±	0,1
	2 PLC	±	0,05
	3 PLC	±	0,01
	4 PLC	±	-
	ANGLES	±	0,2°
MATERIAL		FINISH	
		Pre-tinplated	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[338097-1 \(Loose Piece\)](#)