



REVISIONS				
P	LTR	DESCRIPTION	DATE	APVD
	4	PRODUCTION ISSUE	01FEB2019	PNT MT

a) Part as supplied



b) Part after unrestricted recovery



DIMENSIONS in millimetres
[in inches, for reference]

Part No.	H		J		K		P	R	S	T	HW	JW	KW
	Min	Max	Min	Max	Min	Max	±10%	±10%	±10%	±10%	±20%	±20%	±20%
	a	b	a	b	a	b	b	b	b	b	b	b	b
382W042	20 [0.79]	8.0 [0.31]	9.0 [0.35]	4.0 [0.16]	9.0 [0.35]	4.0 [0.16]	30 [1.18]	32 [1.26]	35 [1.38]	25 [0.98]	2.0 [0.08]	1.25 [0.05]	1.25 [0.05]

RELEASED FOR PUBLICATION

ALL RIGHTS RESERVED.

THIS DRAWING IS UNPUBLISHED.

COPYRIGHT - TE Connectivity Ltd.

DIMENSIONS: mm [INCHES]	DWN PRAVEEN N T	01FEB2019	MATERIAL	SEE SHEET 2	FINISH	-
	CHK N NAGAR	01FEB2019	TE Connectivity Ltd.			
TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD M TAYLOR	01FEB2019				
0 PLC ± -	PRODUCT SPEC	-	NAME			TRANSITION, Y
1 PLC ± -	-	-	SIZE			A4
2 PLC ± -	APPLICATION SPEC	-	CAGE CODE	DRAWING NO	RESTRICTED TO	
3 PLC ± -	-	-	00779	382W042-XX-0	-	
4 PLC ± -	WEIGHT	-	SCALE			DNS
ANGLES ± -	-	-	SHEET			1 OF 2
	CUSTOMER DRAWING	-	REV			4

REVISIONS				
P	LTR	DESCRIPTION	DATE	APVD
	-	SEE SHEET 1	-	-

COMPATIBILITY CHART

Material Dash Number	Material Description	RT Spec	Coating Slash No.	Coating S No.
-3	POLYOLEFIN, SEMI-RIGID	RT-301	/42,/86,/180	S1017;S1048;S1030
-4	POLYOLEFIN, FLEXIBLE	RT-1304	/42,/86,/180	S1017;S1048;S1030
-12	FLUOROELASTOMER, FLEXIBLE	RT-1312	N/A	N/A
-25	ELASTOMER, FLUID RESISTANT	RW-2070	/42,/86,/225	S1017;S1048;S1206
-100	POLYOLEFIN, SEMI-FLEXIBLE ZEROHAL	RW-2082	/86;/180	S1048;S1030

Ordering Information

382W042-XX/XX-0

Color designator
 Adhesive Slash Number (if required see compatibility chart)
 Material Dash Number (see compatibility chart)
 Base Part Number

NOTES

- 1) As supplied dimensions are for uncoated parts, when coating is added entry diameters will reduce by 1.5mm[.06] Max.
- 2) Potting Ports are optional, when specified by suffix "-00" they will be located as shown.


RELEASED FOR PUBLICATION

ALL RIGHTS RESERVED.

© COPYRIGHT - TE Connectivity Ltd.

THIS DRAWING IS UNPUBLISHED.

DIMENSIONS: mm [INCHES]	DWN PRAVEEN N T	01FEB2019	MATERIAL SEE SHEET 2	FINISH -			
	CHK N NAGAR	01FEB2019	TE Connectivity Ltd.				
TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± - 4 PLC ± - ANGLES ± -	APVD M TAYLOR	01FEB2019			NAME TRANSITION, Y		
	PRODUCT SPEC -		SIZE A4	CAGE CODE 00779			DRAWING NO G-382W042-XX-0
	WEIGHT		CUSTOMER DRAWING		SCALE DNS	SHEET 2 OF 2	REV 4



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[382W042-25/225-0](#)