



LOC	QIST	REVISIONS	DATE	BY	APPROV
DY	-	SEE SHEET 1	-	-	-



NOTES:

- ALL DIMENSIONS IN MM
- GENERAL TOL: ± 0.1mm
- MATERIAL: HOUSING THK 0.4mm
- PACKAGING PER REEL: 1115 POCKETS; OD: 330mm, ID: 100mm
- QTY PER REEL: 1000 PCS
- 10 PITCHES CUMULATIVE TOLERANCE ON TAPE ± 0.2mm




- 6 PEELING STRENGTH: 10g-70g
 PEELING ANGLE 165-180
 7 PEELING SPEED: 300mm/MINUTE

8. TAPE & REEL PACKAGING APPLY TO P/N: 1-84108-2, 1-84108-4

TAPE & REEL PACKAGING



SECTION D-D



THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INFORMATION. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING DEPARTMENT HAS THE AUTHORITY TO REVOKE THIS DRAWING.		DWS 05JUL2005 KW YAP CR 05JUL2005 WL CHOO AFV 05JUL2005 SF LEONG	TE Connectivity NAME HEADER ASSEMBLY, 2mm AMPMODU SMT, R/A, D/R	
DIMENSIONS: mm	TOLERANCES UNLESS OTHERWISE SPECIFIED: 3 PLC ±0.2 1 PLC ±0.2 2 PLC ±0.25 3 PLC ±0.3 4 PLC ±0.3 ANGLES ±3° FINISH	PRODUCT SPEC APPLICATION SPEC WEIGHT CUSTOMER DRAWING	SIZE A2	CASE CODE 00779 DRAWING NO C-5084108 SCALE 3:1 SHEET 2 OF 2 REV A1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1-5084108-2](#)