




1	MATERIAL	HOUSING: THERMOPLASTIC, UL 94V-0. POST : BRASS
2	FINISH	CONTACT AREA, "D" MIN Au ON NICKEL 0.0013 MIN ALL OVER POST TINE: 0.002 MIN MATTE TIN
3	POST POSITION NUMBERS FOR REFERENCE ONLY.	



--

DIMENSIONS: mm 		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± 1 PLC ± 2 PLC ± 3 PLC ± 4 PLC ± ANGLES ± FINISH		DWN WYLEE 07MAR2005 CHG VINCENT TAN APVD SEI LONG PRODUCT SPEC - APPLICATION SPEC - WEIGHT - CUSTOMER DRAWING		 TE Connectivity NAME AMPMODU 2mm PITCH POST HDR, VERTICAL MOUNT TYPE SIZE A2 CAGE CODE 00779 DRAWING NO C-5176264 SCALE 8:1 SHEET 1 OF 1 REV P	
MATERIAL 							

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[5176264-3](#)