

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

© COPYRIGHT copyright.dBye

ALL RIGHTS RESERVED.

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	C	REVISED PER ECO-13-015791	10OCT2013	KH	RH
	D	REVISED PER ECO-18-011900	07SEP2018	SR	PO
	E	REVISED PER ECO-20-007796	29DEC2021	GSK	JB

MATERIAL:

HOUSING : 30% G.F. NYLON , COLOUR : NATURAL.
ACTUATOR: 20% G.F. POLYESTER , COLOUR : RED.
CONTACTS: PHOSPHOR-BRONZE.
PLATING: 2,5µmTIN.

⚠

P.C.B. Hole Dim. Action-Pin

Drilled hole: 0,75 ±0,025 mm
Fin. Hole: 0,6 to 0,72 mm
Cu-thickness: 0,025 to 0,05 mm
SN-thickness: 0,004 to 0,01 mm

SWITCH HOUSING MAY HAVE
PROFILE A, B OR C.

A

B

C

SECTION A - A

LASER MARKINGS AS SHOWN

RECOMMENDED P.C.B HOLE PATTERN.
P.C.B THICKNESS : 1,6mm MIN.

OBsolete

PART NUMBER	NUMBER OF POSITIONS	"L" MAX.	"M"
0-5338048-1	1	5,08	-
0-5338048-2	2	7,62	2,54
0-5338048-3	3	10,16	5,08
0-5338048-4	4	12,70	7,62
0-5338048-5	5	15,24	10,16
0-5338048-6	6	17,78	12,70
0-5338048-7	7	20,32	15,24
0-5338048-8	8	22,86	17,78
0-5338048-9	9	25,40	20,32

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN18SEP2007

SA008712

CHK-

APVD-

PRODUCT SPEC-

APPLICATION SPEC-

WEIGHT-

CUSTOMER DRAWING

TE Connectivity

DIP SWITCH
ACTION PIN VERSION

SIZEA200779

CAGE CODEC-C-5338048

DRAWING NO

RESTRICTED TO

SCALE

SHEET

OF

REV

1471-9 (3/13)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[5338048-2](#)