





① MATERIAL ; HOUSING : HIGH TEMP THERMO PLASTIC
UL94V-0
CONTACT : COPPER ALLOY

② FINISH ; UNDER PL Ni 0.0013mm MIN ALL OVER.
CONTACT AREA 0.0002 MIN Au PL.
SOLDERING AREA
SIGNAL POS: 0.00005 MIN Au PL.
⑤ GROUND POS: 0.00005 MIN Au PL.

③ ■ THIS POSITION IS GROUND CIRCUIT.

NOT AVAILABLE	52.6	51.8	25.3	47.4	50	54.7	54.7	320	1-353123-1
AVAILABLE	46.6	45.8	22.3	41.4	44	48.7	48.7	280	1-  -0
NOT AVAILABLE	40.6	39.8	19.3	35.4	38	42.7	42.7	240	 -9
AVAILABLE	34.6	33.8	16.3	29.4	32	36.7	36.7	200	353123-8
TOOLING STATUS	G	F	E	D	C	B	A	POS	CAP P/N

DWN	 TE Connectivity Ltd.			
CHK				
APVD	NAME 名称			
PRODUCT SPEC 製品規格	EMBOSS ASSY FH 0.6BTB CONNECTOR REC. 4H 2ROW TYPE W/G-CONT ONE SIDE BOSS LESS TYPE			
APPLICATION SPEC 取付適用規格	SIZE	CAGE CODE	DRAWING NO 番号	RESTRICTED
WEIGHT	A3	00779	C-5353906	
CUSTOMER DRAWING			SCALE 尺度	SHEET
			2.1	2 OF 3
				REV B

GENERAL TOLERANCE
一般公差

10 ≥ ±0.2
30 ≥ >10: ±0.25
100 ≥ >30: ±0.3
ANGLES: ±3°

4


3

2


1

REVISIONS


P	LTR	DESCRIPTION	DATE	DWN	APVD
	—	SEE SHEET 1	—	—	—




280P



240P




320P



200P

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
単位: 耗
mmMATERIAL
材料TOLERANCES UNLESS
OTHERWISE SPECIFIED:
一般公差

0 PLC	±
1 PLC	±
2 PLC	±
3 PLC	±
4 PLC	±
ANGLES	±

FINISH
仕上

DWN

CHK

APVD

PRODUCT SPEC

製品規格

APPLICATION SPEC

取付適用規格

WEIGHT

CUSTOMER DRAWING



TE Connectivity Ltd.

NAME
名称

EMBOSS ASSY

FH 0.6BTB CONNECTOR REC. 4H 2ROW TYPE
W/G-CONT ONE SIDE BOSS LESS TYPE

SIZE

A3

CAGE CODE

00779

DRAWING NO

番号

C=5353906

RESTRICTED TO

SCALE
尺度

3:1

SHEET

3 OF 3

REV

B

GENERAL TOLERANCE
一般公差

10≥	±0.2
30≥	>10:±0.25
100≥	>30:±0.3
ANGLES:±3°	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1-5353906-0](#)