




D

C

B

A

D

C

B

A

THIS DRAWING IS UNPUBLISHED.	RELEASED FOR PUBLICATION
© COPYRIGHT - By -	ALL RIGHTS RESERVED.

LOC	DIST	REVISIONS					
AD	00	P	LTR	DESCRIPTION	DATE	DWN	APVD
			—	SEE SHEET 1	—	—	—

	99.06	3.900	101.60	4.000	80		9-535542-0
	96.52	3.800	99.06	3.900	78		8-535542-9
	93.98	3.700	96.52	3.800	76		8-535542-8
	91.44	3.600	93.98	3.700	74		8-535542-7
	88.90	3.500	91.44	3.600	72		8-535542-6
	86.36	3.400	88.90	3.500	70		8-535542-5
	83.82	3.300	86.36	3.400	68		8-535542-4
	81.28	3.200	83.82	3.300	66		8-535542-3
	78.74	3.100	81.28	3.200	64		8-535542-2
	76.20	3.000	78.74	3.100	62		8-535542-1
	73.66	2.900	76.20	3.000	60		8-535542-0
	71.12	2.800	73.66	2.900	58		7-535542-9
	68.58	2.700	71.12	2.800	56		7-535542-8
	66.04	2.600	68.58	2.700	54		7-535542-7
	63.50	2.500	66.04	2.600	52		7-535542-6
	60.96	2.400	63.50	2.500	50		7-535542-5
	58.42	2.300	60.96	2.400	48		7-535542-4
	55.88	2.200	58.42	2.300	46		7-535542-3
	53.34	2.100	55.88	2.200	44		7-535542-2
	50.80	2.000	53.34	2.100	42		7-535542-1
	48.26	1.900	50.80	2.000	40		7-535542-0
	45.72	1.800	48.26	1.900	38		6-535542-9
	43.18	1.700	45.72	1.800	36		6-535542-8
	40.64	1.600	43.18	1.700	34		6-535542-7
	38.10	1.500	40.64	1.600	32		6-535542-6
	35.56	1.400	38.10	1.500	30		6-535542-5
	33.02	1.300	35.56	1.400	28		6-535542-4
	30.48	1.200	33.02	1.300	26		6-535542-3
	27.94	1.100	30.48	1.200	24		6-535542-2
	25.40	1.000	27.94	1.100	22		6-535542-1
	22.86	.900	25.40	1.000	20		6-535542-0
	20.32	.800	22.86	.900	18		5-535542-9
	17.78	.700	20.32	.800	16		5-535542-8
	15.24	.600	17.78	.700	14		5-535542-7
	12.70	.500	15.24	.600	12		5-535542-6
	10.16	.400	12.70	.500	10		5-535542-5
	7.62	.300	10.16	.400	8		5-535542-4
	5.08	.200	7.62	.300	6		5-535542-3
	2.54	.100	5.08	.200	4		5-535542-2
	-		2.54	.100	2		5-535542-1
FINISH	B	A	NO OF POSN	PART NUMBER			

	2	99.06[3.900]	101.60[4.000]	80	4-535542-0
	2	96.52[3.800]	99.06[3.900]	78	3-535542-9
	2	93.98[3.700]	96.52[3.800]	76	3-535542-8
	2	91.44[3.600]	93.98[3.700]	74	3-535542-7
	2	88.90[3.500]	91.44[3.600]	72	3-535542-6
	2	86.36[3.400]	88.90[3.500]	70	3-535542-5
	2	83.82[3.300]	86.36[3.400]	68	3-535542-4
	2	81.28[3.200]	83.82[3.300]	66	3-535542-3
	2	78.74[3.100]	81.28[3.200]	64	3-535542-2
	2	76.20[3.000]	78.74[3.100]	62	3-535542-1
	2	73.66[2.900]	76.20[3.000]	60	3-535542-0
	2	71.12[2.800]	73.66[2.900]	58	2-535542-9
	2	68.58[2.700]	71.12[2.800]	56	2-535542-8
	2	66.04[2.600]	68.58[2.700]	54	2-535542-7
	2	63.50[2.500]	66.04[2.600]	52	2-535542-6
	2	60.96[2.400]	63.50[2.500]	50	2-535542-5
	2	58.42[2.300]	60.96[2.400]	48	2-535542-4
	2	55.88[2.200]	58.42[2.300]	46	2-535542-3
	2	53.34[2.100]	55.88[2.200]	44	2-535542-2
	2	50.80[2.000]	53.34[2.100]	42	2-535542-1
	2	48.26[1.900]	50.80[2.000]	40	2-535542-0
	2	45.72[1.800]	48.26[1.900]	38	1-535542-9
	2	43.18[1.700]	45.72[1.800]	36	1-535542-8
	2	40.64[1.600]	43.18[1.700]	34	1-535542-7
	2	38.10[1.500]	40.64[1.600]	32	1-535542-6
	2	35.56[1.400]	38.10[1.500]	30	1-535542-5
	2	33.02[1.300]	35.56[1.400]	28	1-535542-4
	2	30.48[1.200]	33.02[1.300]	26	1-535542-3
	2	27.94[1.100]	30.48[1.200]	24	1-535542-2
	2	25.40[1.000]	27.94[1.100]	22	1-535542-1
	2	22.86[.900]	25.40[1.000]	20	1-535542-0
	2	20.32[.800]	22.86[.900]	18	535542-9
	2	17.78[.700]	20.32[.800]	16	535542-8
	2	15.24[.600]	17.78[.700]	14	535542-7
	2	12.70[.500]	15.24[.600]	12	535542-6
10	2	10.16[.400]	12.70[.500]	10	535542-5
10	2	7.62[.300]	10.16[.400]	8	535542-4
10	2	5.08[.200]	7.62[.300]	6	535542-3
10	2	2.54[.100]	5.08[.200]	4	535542-2
10	2	-	2.54[.100]	2	6 535542-1
FINISH	B	A	NO OF POSN	PART NUMBER	

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN M.BINNER		06NOV2002		 TE Connectivity	
DIMENSIONS: mm [INCHES]		CHK J.OLSON		06NOV02			
	TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD J.OLSON		06NOV02		NAME RECEPTACLE ASSEMBLY, MOD IV, DOUBLE ROW, DUAL ENTRY, .100X.100CL, VERTICAL MOUNT, AMPMODU
	0 PLC ± - 1 PLC ± - 2 PLC ± 0.13[.005] 3 PLC ± - 4 PLC ± - ANGLES ± -		PRODUCT SPEC 108-25022				
	MATERIAL 		APPLICATION SPEC 114-25018		SIZE A2		
FINISH  		WEIGHT -		DRAWING NO C-535542		RESTRICTED TO -	
CUSTOMER DRAWING				SCALE 1:1		SHEET 2 of 2	
				REV U5			

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[3-535542-8](#)