

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	R	PRODUCTION ISSUE	31JAN2019	PNT	MT





TABLE OF DIMENSIONS


PART NUMBER	H		J,K,L & N		P	R	S	T	U	C*	D*	HW	W	Weight Nom lb/[gms]
	Min	Max	Min	Max	±10%	±10%	±10%	±10%	±10%	±5%	±5%	±20%	±20%	
	a	b	a	b	b	b	b	b	b	b	b	b	b	b
562A011	13.2 [.52]	6.9 [.27]	6.6 [.26]	3.5 [.14]	24.1 [.95]	38.4 [1.51]	24.1 [.95]	43.9 [1.73]	20.0 [.79]	45	15	1.52 [.06]	1.02 [.04]	3.63 [.008]
562A022	19.3 [.76]	9.7 [.38]	9.4 [.37]	5.3 [.21]	35.6 [1.40]	36.1 [1.42]	32.0 [1.26]	43.2 [1.70]	23.1 [.91]	45	15	1.78 [.07]	1.02 [.04]	6.80 [.015]
562A032	19.3 [.76]	9.7 [.38]	13.2 [.52]	6.9 [.27]	49.3 [1.94]	36.1 [1.42]	45.0 [1.77]	50.5 [1.99]	25.4 [1.00]	45	15	1.78 [.07]	1.52 [.06]	13.61 [.030]
562A043	26.9 [1.06]	13.0 [.51]	13.2 [.52]	6.9 [.27]	49.3 [1.94]	51.8 [2.04]	45.0 [1.77]	65.8 [2.59]	33.5 [1.32]	45	15	2.54 [.10]	1.52 [.06]	18.60 [.041]
562A054	38.6 [1.52]	18.5 [.73]	19.3 [.76]	9.7 [.38]	71.9 [2.83]	74.9 [2.95]	65.3 [2.57]	95.3 [3.75]	46.5 [1.83]	45	15	3.05 [.12]	1.78 [.07]	54.43 [1.20]
562A067	55.6 [2.19]	26.7 [1.05]	26.9 [1.06]	13.0 [.51]	101.6 [4.00]	108.5 [4.27]	92.5 [3.64]	135.1 [5.32]	65.5 [2.58]	45	15	4.57 [.18]	2.54 [.10]	149.69 [3.30]

DIMENSIONS:

mm [INCHES]

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ± -
 1 PLC ± -
 2 PLC ± -
 3 PLC ± -
 4 PLC ± -
 ANGLES ± -



DWN 31JAN2019

PRAVEEN N T

CHK 31JAN2019

N NAGAR

APVD 31JAN2019

M TAYLOR

PRODUCT SPEC

-

APPLICATION SPEC

-

WEIGHT

MATERIAL

SEE SHEET 2

FINISH

-



TE Connectivity Ltd.

NAME

TRANSITION, 1 TO 4 CABLES

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

A4

00779

C-

562A011-XX-0THRU067-XX-0

-

CUSTOMER DRAWING

SCALE

DNS

SHEET

1 OF 2

REV


R

COMPATABILITY CHART				
MATERIAL DASH NO.	MATERIAL DESCRIPTION	RT SPEC	COATINGS/SLASHNO.	COATINGSNO.
-3	Polyolefin, Semi-rigid	RT-301	/42;/86;/180	S1017;S1048;S1030
-4	Polyolefin, Flexible	RT-1304	/42;/86;/180	S1017;S1048;S1030
-12	Fluoroelastomer, flexible	RT-1312	N/A	N/A
-25	Elastomer, Fluid Resistant	RW-2070	/42;/86;/225	S1017;S1048;S1206
-100	Polyolefin, Semi-flexible ZEROHAL	RW-2082	/86;/180	S-1048;S-1030

Diagram illustrating the breakdown of the part number 562A0XX-XX-XX/XX-0 into its components:

- Base part number: 562A0XX
- Material dash number (See Compatibility Chart): -XX
- Modification number: -XX
- Adhesive slash number (If necessary, see Compatibility Chart): /XX
- Color designator: -0

1. Dimensions appearing in table are as follows:
 - a - As Supplied
 - b - After Unrestricted Recovery
2. Coating is optional. As supplied dimensions appearing in table are for uncoated parts. When coating is added, entry diameters will be reduced by 1.5mm[.06"] max.
3. Molding ports are optional. When -00 modification number is specified molding ports will be located as shown.
4. Weight appearing in table of dimensions is based on polyolefin part.

DIMENSIONS: mm [INCHES]		DWN PRAVEEN N T	31JAN2019	MATERIAL —		FINISH —	
TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± — 1 PLC ± — 2 PLC ± — 3 PLC ± — 4 PLC ± — ANGLES ± —		CHK N NAGAR	31JAN2019	TE Connectivity Ltd.			
		APVD M TAYLOR	31JAN2019				
		PRODUCT SPEC —		NAME TRANSITION, 1 TO 4 CABLES —			
		APPLICATION SPEC —					
		WEIGHT		SIZE A4	CAGE CODE 00779	DRAWING NO C-562A011-XX-0THRU067-XX-0	RESTRICTED TO —
		CUSTOMER DRAWING			SCALE DNS	SHEET 2 OF 2	REV R

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[562A022-3/42-0](#)