

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	R	PRODUCTION ISSUE	31JAN2019	PNT	MT





TABLE OF DIMENSIONS

PART NUMBER	H		J,K,L & N		P	R	S	T	U	C*	D*	HW	W	Weight Nom lb/[gms]
	Min	Max	Min	Max	±10%	±10%	±10%	±10%	±10%	±5%	±5%	±20%	±20%	
	a	b	a	b	b	b	b	b	b	b	b	b	b	b
562A011	13.2 [.52]	6.9 [.27]	6.6 [.26]	3.5 [.14]	24.1 [.95]	38.4 [1.51]	24.1 [.95]	43.9 [1.73]	20.0 [.79]	45	15	1.52 [.06]	1.02 [.04]	3.63 [.008]
562A022	19.3 [.76]	9.7 [.38]	9.4 [.37]	5.3 [.21]	35.6 [1.40]	36.1 [1.42]	32.0 [1.26]	43.2 [1.70]	23.1 [.91]	45	15	1.78 [.07]	1.02 [.04]	6.80 [.015]
562A032	19.3 [.76]	9.7 [.38]	13.2 [.52]	6.9 [.27]	49.3 [1.94]	36.1 [1.42]	45.0 [1.77]	50.5 [1.99]	25.4 [1.00]	45	15	1.78 [.07]	1.52 [.06]	13.61 [.030]
562A043	26.9 [1.06]	13.0 [.51]	13.2 [.52]	6.9 [.27]	49.3 [1.94]	51.8 [2.04]	45.0 [1.77]	65.8 [2.59]	33.5 [1.32]	45	15	2.54 [.10]	1.52 [.06]	18.60 [.041]
562A054	38.6 [1.52]	18.5 [.73]	19.3 [.76]	9.7 [.38]	71.9 [2.83]	74.9 [2.95]	65.3 [2.57]	95.3 [3.75]	46.5 [1.83]	45	15	3.05 [.12]	1.78 [.07]	54.43 [.120]
562A067	55.6 [2.19]	26.7 [1.05]	26.9 [1.06]	13.0 [.51]	101.6 [4.00]	108.5 [4.27]	92.5 [3.64]	135.1 [5.32]	65.5 [2.58]	45	15	4.57 [.18]	2.54 [.10]	149.69 [.330]

DIMENSIONS:

mm [INCHES]

DWN

PRAVEEN N T

31JAN2019

MATERIAL

SEE SHEET 2

FINISH

-

CHK

N NAGAR

31JAN2019

APVD

M TAYLOR

31JAN2019

PRODUCT SPEC

-

APPLICATION SPEC

-

WEIGHT

NAME

TRANSITION, 1 TO 4 CABLES

SIZE

A4

CAGE CODE

00779

DRAWING NO

C-

562A011-XX-0THRU067-XX-0

RESTRICTED TO

-

CUSTOMER DRAWING

SCALE

DNS

SHEET

1 OF 2


REV

R

THIS DRAWING IS UNPUBLISHED.

ALL RIGHTS RESERVED.

COPYRIGHT - BY -




COMPATABILITY CHART				
MATERIAL DASH NO.	MATERIAL DESCRIPTION	RT SPEC	COATINGS LASH NO.	COATINGS NO.
-3	Polyolefin, Semi-rigid	RT-301	/42;/86;/180	S1017;S1048;S1030
-4	Polyolefin, Flexible	RT-1304	/42;/86;/180	S1017;S1048;S1030
-12	Fluoroelastomer, flexible	RT-1312	N/A	N/A
-25	Elastomer, Fluid Resistant	RW-2070	/42;/86;/225	S1017;S1048;S1206
-100	Polyolefin, Semi-flexible ZEROHAL	RW-2082	/86;/180	S-1048;S-1030

Diagram illustrating the breakdown of a part number into its components:

- Base part number: 562A0XX
- Material dash number (See Compatibility Chart): -XX
- Modification number: -XX
- Adhesive slash number (If necessary, see Compatibility Chart): /XX
- Color designator: -0

1. Dimensions appearing in table are as follows:
 - a - As Supplied
 - b - After Unrestricted Recovery
2. Coating is optional. As supplied dimensions appearing in table are for uncoated parts. When coating is added, entry diameters will be reduced by 1.5mm[.06"] max.
3. Molding ports are optional. When -00 modification number is specified molding ports will be located as shown.
4. Weight appearing in table of dimensions is based on polyolefin part.

DIMENSIONS:		DWN	31JAN2019	MATERIAL		FINISH	
mm [INCHES]		PRAVEEN N T		-		-	
TOLERANCES UNLESS OTHERWISE SPECIFIED:		CHK	31JAN2019	 TE Connectivity Ltd.			
		APVD	31JAN2019				
		M TAYLOR		NAME TRANSITION, 1 TO 4 CABLES -			
		PRODUCT SPEC					
0 PLC ± -		-		SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
1 PLC ± -		APPLICATION SPEC		A4	00779	 562A011-XX-0THRU067-XX-0	-
2 PLC ± -		-					
3 PLC ± -		WEIGHT		CUSTOMER DRAWING			
4 PLC ± -		-		SCALE	DNS	SHEET	2 OF 2
ANGLES ± -				REV		R	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[562A011-3/42-0](#)