

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

— , — .

© COPYRIGHT — TE Connectivity Ltd.

ALL RIGHTS RESERVED.

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	N	REV PER ECR 07-027142	12NOV07	JR	TM
	N1	REVISED PER ECO-17-016703	03APR2018	RS	DR
	N2	REVISED PER ECO-18-011826	26JUL2018	RS	DR

AMP

WIRE RANGE

22-16 AWG
STRANDED

8.992 [.354]
MIN

43.002 [1.693] MAX

8.992 [.354]
MIN

EXPANDED I.D

AMP 22-16

AMP 22-16

AMP 22-16

HEAT SHRINKABLE
TUBING

COPPER SPLICE

1 TUBING MATERIAL; CROSS-LINKED POLYMER WITH MELT LINER; COLOR, RED; BLACK INK LEGEND 1/16 MIN; HEIGHT; ONE FULL APPEARANCE MIN.

2 TEMP RATING -65°F TO 257°F [-55°C TO 125°C]

3 NOTE DELETED

4 SHIPPING WEIGHT [0.076].003 LBS EACH

5 VOLTAGE RATING: 600 V MAX
(1000 V MAX FIXTURES & SIGNS)

△6 MATERIAL & FINISH ; BODY — COPPER, TIN PLATED SLEEVE — NYLON

7 NOTE DELETED

LOOSE PIECE	4.445 [.175]	1.651 [.065]	1000	603502-3
SMALL PACK	4.445 [.175]	1.651 [.065]	50/BOX	603502-2
PACKAGE TYPE	EXPANDED I.D. MIN	RECOVERED I.D. MAX	QTY	PART NO.

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm [INCHES]

0 PLC ± —

1 PLC ± —

2 PLC ± 0.51 [.02]

3 PLC ± 0.127[.005]

4 PLC ± —

ANGLES ± —

FINISH

△6

△6

DWN JR RUTH 24JUN04

CHK T MICHELUTTI 24JUN04

APVD T MICHELUTTI 24JUN04

PRODUCT SPEC —

APPLICATION SPEC —

WEIGHT

STE

TE Connectivity Ltd.

PRE-INSULATED SEALED SPLICE
WIRE SIZE: 22-16 AWG

SIZE A3

CAGE CODE 00779

DRAWING NO C-603502

RESTRICTED TO —

CUSTOMER DRAWING

SCALE 1:1

SHEET 1 OF 1

REV N2

1470-19 (1/15)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[603502-2](#)