




LOC	DIST	REVISIONS				
G	14	P	LTR	DESCRIPTION	DATE	APVD
			F1	REVISED PER ECO-11-004820	11MAR11	RK HMR




1 . INSULATION DIA .135 MAX

2 . FITS TAB .020 THK



100	LOOSE PC,BOX	8-640909-1
-	TAPE MOUNTED	640909-2
-	LOOSE PIECE	640909-1
QTY	PACKAGE TYPE	PART NO

AMP INCORPORATED CUSTOMER SERVICE SYSTEM		MAX RECOMMENDED OPERATING TEMPERATURE: -	THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN L OLMEDA 26JUN95	 TE Connectivity				
FOR ADDITIONAL PRODUCT INFORMATION OR COPIES OF DRAWINGS AND TECHNICAL DOCUMENTS	PRODUCT INFORMATION CENTER 1-800-522-6752	VOLTAGE RATING: - -	DIMENSIONS: INCHES	TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± - 1 PLC ± - 2 PLC ± .015 3 PLC ± - 4 PLC ± - ANGLES ± -	CHK M ELLIS 26JUN95	NAME RECEPTACLE, 205 SERIES, FASTON™, PIDG™, WIRE SIZE,22-18 AWG				
	FOR APPLICATION TOOLING INFORMATION	TOOLING ASSISTANCE CENTER 1-800-722-1111	CIRCULAR MIL AREA: - -							APVD B BARE 26JUN95
FOR ORDER ENTRY		1-800-526-5142		MATERIAL BODY,BRASS .016 SLV,NYLON,COLOR, RED	FINISH BODY,TIN	PRODUCT SPEC -	APPLICATION SPEC -	WEIGHT -	SIZE A3	CAGE CODE 00779
CUSTOMER DRAWING					SCALE NTS		SHEET 1 OF 1		REV F1	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[8-640909-1](#)