





D



REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	H1	REVISED PER ECR-16-011494	22JUN2017	NK	CX
	H2	ECO-19-006502	30APR2019	AP	WLS
	H3	REVISED PER ECO-20-009852	14JUL2020	WLS	DZ
	H4	REVISED PER ECN-21-100661	25MAR2021	WLS	VS



C



- 1 MATERIAL;
HOUSING - UL 94V-0 RATED HIGH TEMP NYLON, COLOR BLACK.
CONTACTS - BRASS.
HOLDDOWNS - PHOSPHOR BRONZE.
- 2 DIMENSION APPLIES TO SOLDERTAIL SURFACES AND STANDOFF SURFACES.
- 3 RECOMMENDED PC BOARD THICKNESS OF 1.57.
- 4 ALL SOLDERTAILS AND HOLDDOWNS.
- 5 PLATING;
CONTACTS - 0.38µm MINIMUM GOLD ON MATING AREA.
2.54µm MINIMUM MATTE TIN ON SOLDER TAIL.
ALL OVER 1.27µm MINIMUM NICKEL.
HOLDDOWNS - 2.54µm MINIMUM MATTE TIN OVER 1.27µm MINIMUM NICKEL.

- 6 COUNTERPART RECOMMENDED IS PN 794617 (DASH ACCORDING TO NUMBER OF POSITION).
- 7 FOR REELING DIRECTION AND PACKAGING TYPE, SEE SPECIFICATION 114-13000.

B

36.86	40.79	33.00	40.00	24	5-794628-4
33.86	37.79	30.00	37.00	22	5-794628-2
30.86	34.79	27.00	34.00	20	5-794628-0
27.86	31.79	24.00	31.00	18	4-794628-8
24.86	28.79	21.00	28.00	16	4-794628-6
21.86	25.79	18.00	25.00	14	4-794628-4
18.86	22.79	15.00	22.00	12	4-794628-2
15.86	19.79	12.00	19.00	10	4-794628-0
12.86	16.79	9.00	16.00	8	3-794628-8
9.86	13.79	6.00	13.00	6	3-794628-6
6.86	10.79	3.00	10.00	4	3-794628-4
3.86	7.79	-	7.00	2	3-794628-2
DIM Y	DIM W	DIM Z	DIM X	NO. OF POSN.	PART NUMBER

A

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:

mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ±

1 PLC ±

2 PLC ±0.13

3 PLC ±

4 PLC ±

ANGLES ±1°

FINISH

DWN K. WHITAKER 19MAR2003

CHK C. JONES 19MAR2003

APVD C. JONES 19MAR2003

PRODUCT SPEC 108-1836

APPLICATION SPEC 114-13000

WEIGHT -


CUSTOMER DRAWING

TE Connectivity

NAME SURFACE MOUNT,RIGHT ANGLE,SURFACE MOUNT HOLDDOWN,ASSEMBLY,15 GOLD HEADER,DUAL ROW,MICRO MATE-N-LOK TM

SIZE A2 CAGE CODE 00779 DRAWING NO. 794628 RESTRICTED TO -

SCALE 4:1 SHEET 1 OF 2 REV H4



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1-794628-2](#)