



8		7		
THIS DRAWING IS UNPUBLISHED.		RELEASED FOR PUBLICATION		
© COPYRIGHT N/A		BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.		
PART NO.		'A' 	'B'	REMARKS
862545-1	6.00	[152.4]	.38 [9.7]	
862545-2	8.00	[203.2]	.38 [9.7]	
862545-3	10.00	[254.0]	.38 [9.7]	
862545-4	12.00	[304.8]	.38 [9.7]	
862545-5	15.00	[381.0]	.38 [9.7]	
862545-6	18.00	[457.2]	.38 [9.7]	
862545-7	21.00	[533.4]	.38 [9.7]	
862545-8	24.00	[609.6]	.38 [9.7]	
862545-9	4.50	[114.3]	.50 [12.7]	OBSOLETE
1-862545-0	11.00	[279.4]	.25 [6.3]	
1-862545-1	48.00	[1219.2]	.38 [9.7]	
1-862545-2	20.00	[508.0]	.38 [9.7]	OBSOLETE
1-862545-3	13.00	[330.2]	.38 [9.7]	
1-862545-4	14.00	[355.6]	.38 [9.7]	
1-862545-5	600.00	[15240.0]	.38 [9.7]	OBSOLETE
1-862545-6	16.00	[406.4]	.38 [9.7]	
1-862545-7	5.00	[127.0]	.38 [9.7]	
1-862545-8	36.00	[914.4]	.38 [9.7]	
1-862545-9	60.00	[1524.0]	.38 [9.7]	
2-862545-0	84.00	[2133.6]	.38 [9.7]	OBSOLETE
2-862545-1	7.50	[190.5]	.38 [9.7]	
2-862545-2	30.00	[762.0]	.38 [9.7]	
2-862545-3	9.00	[228.6]	.38 [9.7]	
2-862545-4	14.50	[368.3]	.38 [9.7]	
2-862545-5	22.00	[558.8]	.38 [9.7]	
2-862545-6	17.63	[447.8]	.38 [9.7]	
2-862545-7	11.63	[295.4]	.38 [9.7]	OBSOLETE
2-862545-8	72.00	[1828.8]	.38 [9.7]	
2-862545-9	33.00	[838.2]	.38 [9.7]	
3-862545-0	19.00	[482.6]	.38 [9.7]	OBSOLETE
3-862545-1	37.00	[939.8]	.38 [9.7]	OBSOLETE
3-862545-2	9.50	[241.3]	.38 [9.7]	OBSOLETE
3-862545-3	6.13	[155.7]	.38 [9.7]	OBSOLETE
3-862545-4	4.00	[101.6]	.38 [9.7]	
3-862545-5	40.00	[1016.0]	.38 [9.7]	OBSOLETE
3-862545-6	7.00	[177.8]	.38 [9.7]	OBSOLETE
3-862545-7	28.00	[711.2]	.38 [9.7]	OBSOLETE
3-862545-8	31.00	[787.4]	.38 [9.7]	OBSOLETE
3-862545-9	240.00	[6096.0]	.38 [9.7]	
4-862545-0	16.63	[422.4]	.38 [9.7]	OBSOLETE
4-862545-1	108.00	[2743.2]	.38 [9.7]	
4-862545-2	17.00	[431.8]	.38 [9.7]	OBSOLETE
4-862545-3	360.00	[9144.0]	.38 [9.7]	OBSOLETE
4-862545-4	79.00	[2006.6]	.38 [9.7]	OBSOLETE
4-862545-5	6.50	[165.1]	.38 [9.7]	
4-862545-6	96.00	[2438.4]	.38 [9.7]	
4-862545-7	144.00	[3657.6]	.38 [9.7]	
5-862545-1	6.00	[152.4]	.38 [9.7]	
5-862545-2	8.00	[203.2]	.38 [9.7]	
5-862545-4	12.00	[304.8]	.38 [9.7]	
5-862545-6	18.00	[457.2]	.38 [9.7]	
5-862545-8	24.00	[609.6]	.38 [9.7]	
6-862545-0	11.00	[279.4]	.25 [6.3]	
6-862545-4	14.00	[355.6]	.38 [9.7]	
6-862545-7	5.00	[127.0]	.38 [9.7]	
6-862545-8	36.00	[914.4]	.38 [9.7]	
7-862545-1	7.50	[190.5]	.38 [9.7]	
7-862545-4	14.50	[368.3]	.38 [9.7]	



-  TOLERANCE OF LEAD LENGTH:
UP TO 24 INCHES [609.6] = ±.12 [±3.0]
24 INCHES [609.6] & UP = ±1%
2. MARKED PER MIL-STD-130.
3. TO MATE WITH AMP LGH-1/2 RECEPTACLE WITH .53 BARREL DEPTH.
-  WHERE APPLICABLE PIGTAIL IS SOLDER DIPPED.
5. OPERATING VOLTAGE: 10 KVDC AT 0 TO 70,000 FEET, -55°C TO 125°C.
-  INSULATION CUT TO LENGTH, BUT NOT REMOVED.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN C.C.THOMAS 16-NOV-89	tyco Electronics		Tyco Electronics Corporation Harrisburg, Pa 17105-3608	
DIMENSIONS: INCHES		CHK D. EABY 01-DEC-89	APVD D. EABY 01-DEC-89		NAME	
		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± - 1 PLC ± - 2 PLC ± .02 [0.5] 3 PLC ± - 4 PLC ± - ANGLES ± - ± - FINISH SEE CALLOUTS		PRODUCT SPEC APPLICATION SPEC		SIZE A1
MATERIAL SEE CALLOUTS		WEIGHT -		CAGE CODE 00779		DRAWING NO 862545
CUSTOMER DRAWING				SCALE 3:1	SHEET 1 OF 1	REV AD

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[862545-6](#)