



LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
AD	00		J2	REVISED ECO-10-018971	17SEP10	HMR	JO



SECTION X-X



RECOMMENDED BOARD MOUNTING  
(RECOMMENDED BOARD THICKNESS: .055-.070)

- 1

2



3

4
- POINT OF MEASUREMENT FOR PLATING THICKNESS (INSIDE OF BEAMS).

TOLERANCE NON-CUMULATIVE.

THE MATING END OF THE CONTACT IS IDENTIFIED BY THE LETTER "A" STAMPED ON THE RECEPTACLE BOX.

OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI



OBSOLETE 4	3.120	2.964	20	2-87984-0
	2.964	2.808	19	-1-87984-9-
	2.808	2.652	18	-1-87984-8-
	2.652	2.496	17	-1-87984-7-
	2.496	2.340	16	-1-87984-6-
	2.340	2.184	15	-1-87984-5-
	2.184	2.028	14	-1-87984-4-
	2.028	1.872	13	-1-87984-3-
	1.872	1.716	12	-1-87984-2-
	1.716	1.560	11	-1-87984-1-
	1.560	1.404	10	-1-87984-0-
	1.404	1.248	9	87984-9
	1.248	1.092	8	87984-8
	1.092	.936	7	87984-7
	.936	.780	6	87984-6
	.780	.624	5	87984-5
	.624	.468	4	87984-4
	.468	.312	3	87984-3
	.312	.156	2	87984-2
B		A	NO OF POSN	ASSEMBLY PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.				DWN L D RINGLEY 17MAR86	Tyco Electronics Corporation Harrisburg, PA 17105-3608			
DIMENSIONS: INCHES				CHK P C DEJONG 18MAR86				
				APVD P C DEJONG 18MAR86	NAME			
				PRODUCT SPEC 108-25,016	ASSY, MOD I, BOARD MOUNT RECP, .156CL, STD PRESSURE, TYPE A, FOR ROUND HOLE MOUNTING			
MATERIAL: HOUSING-FLAME RETARDANT THERMOPLASTIC, COLOR-BLACK CONTACTS: PHOS BRONZE				APPLICATION SPEC 114-25,004	SIZE A2			
FINISH: .000030 GOLD IN THE CONTACT AREA, GOLD FLASH ON THE REMAINDER, ALL OVER .000050 NICKEL				WEIGHT -	CAGE CODE 00779			
CUSTOMER DRAWING				DRAWING NO C=87984				RESTRICTED TO -
				SCALE 4:1				SHEET 1 OF 1
				REV J2				

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[87984-4](#)