




NOTES

- 1. MATERIAL:HOUSING:GLASS FILED THERMO PLASTIC,POLYESTER(94V-0),COLOR:BLACK
CONTACT: COPPER ALLOY
RETENTION LEG: COPPER ALLOY
- 2. FINISH(CONTACT AREA):0.38μmMIN GOLD PLATING OVER Ni PLATING
- 3. FINISH(CONTACT AREA):0.76μmMIN GOLD PLATING OVER Ni PLATING
- 4. FINISH(CONTACT AREA):2.0 μmMIN TIN PLATED OVER NICKEL
- 5. ~~FINISH(RETENTION LEG): TIN LEAD PLATED (CONTACT TAIL) OVER NICKEL~~
- 6. FINISH(RETENTION LEG): TIN PLATED (CONTACT TAIL) OVER NICKEL

注記

- 1. 材料:ハウジング: ガラス入り熱可塑性ポリエスデル樹脂 (94V-0),色: 黒
コンタクト: 銅合金
リテンションレグ: 銅合金
- 2. めっき: コンタクト: 全面Ni下地
接触部: 0.38μm MIN金めっき
- 3. めっき: コンタクト: 全面Ni下地
接触部: 0.76μm MIN金めっき
- 4. めっき: コンタクト: 全面Ni下地
接触部: 2.0 μm MINスズめっき
- 5. めっき: リテンションレグとコンタクト半田付部
ニッケル下地の上に半田めっき
- 6. めっき: リテンションレグとコンタクト半田付部 : ニッケル下地の上にスズめっき

A ROW		X	Y		3-917657-5
B ROW					3-917657-3
A ROW		Y	Y		2-917657-5
B ROW					2-917657-3
A ROW		X	X		1-917657-5
B ROW					1-917657-3
					1-917657-2

KEYING LOCATION	A ROW KEYING	B ROW KEYING	FINISH	製品番号	PART NO.
TE Connectivity					
WIRE RANGE	INSULATION DIA	NAME ダイナミック D-3200 垂直タイプ 10 極 ヘッダーアセンブリー			
MATERIAL SEE NOTE 注記参照	FINISH SEE NOTE 注記参照	DYNAMIC D-3200 10 POS.V-HDR ASS'Y			
		一般公差 (GENERAL TOLERANCE)	SIZE	LOC	NUMBER
		10mm以下 ±0.3	A3	J	C=917657
		10mm超 30mm以下 ±0.4			
		30mm超 100mm以下 ±0.4, 5			
		角度 ±3°			
		SCALE	REV.		SHEET
		2-1	B1		1 OF 1

B1	REVISED PER ECO-11-005030	RK	HMR	26MAR11	DR.	24/APR/'95	DE.	24/APR/'95
LTR	REVISION RECORD	DR	CHK	DATE	CHK.	24/APR/'95	APP.	24/APR/'95
					S.MANABE		S.MANABE	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[3-917657-5](#)