



REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	NC	NEW RELEASE PER E.O. P16085	06MAY1999	-	RDR
	A	REVISED PER E.O. P20438	18MAY2010	-	RDR
	B	REVISED PER PCN E-20-009825	09JUL2020	PMV	IG

D

C

B

A



7. SECONDARY WEDGE LOCK SOLD SEPARATELY: W12P-XXXX.
(XXXX = ALL MODIFICATIONS)

6 RECOMMENDED SCREW: 6-32 [M4].
RECOMMENDED TORQUE: 20-25 IN-LB [2.26-2.82 Nm].


5 MATERIAL - HOUSING: PA66 GF15
GROMMET: VMQ (ORANGE RED)

4. THIS RECEPTACLE MATES WITH DT06-12SA-XXXX PLUG.
(A KEY; XXXX = ALL MODIFICATIONS)
CONSULT FACTORY FOR MODIFICATIONS.

3 FOR CONTACT AND WIRE PERFORMANCE AND APPLICATION
CHARACTERISTICS, SEE ENVELOPE DRAWING 0425-015-0000.

2. DELETED

NOTES : 1. DELETED



SCALE 1:1

3-DIMENSIONAL VIEW

CONTACT SIZE	MIN. INSUL. O.D.	MAX. INSUL. O.D.	WIRE RANGE [mm ²]
16	.088 [2.23]	.145 [3.68]	14-20 AWG [2.0-0.5]

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN S THEIS CHK R MCCORD APVD S BEARD	29APR1999 14MAY2010 04MAY2010	TE Connectivity	
DIMENSIONS: INCHES[MM]	TOLERANCES UNLESS OTHERWISE SPECIFIED:	PRODUCT SPEC	108-151009	NAME 12 WAY RECEPTACLE LE14 MOD COLOR: BLACK -A- KEY ARR. DT SERIES	
		APPLICATION SPEC	114-151009	SIZE	CAGE CODE
		WEIGHT	-	A2	00779
MATERIAL	FINISH	CUSTOMER DRAWING		SCALE	2:1
				SHEET	OF
				REV	B

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[DT04-12PA-LE14](#)