






P	LTR	DESCRIPTION	DATE	DWN	APVD
	AI	ECR-21-108593	07JUL2021	DRK	IG




3D VIEW




- 4 RECOMMENDED SCREW: 2-28 [M2.26X0.91]. PLASTITE 48, SINGLE HELIX
RECOMMENDED TORQUE: 0.75-1.5 IN-LB [0.08-0.16 N-m]
- 3 THE RECEPTACLE MATES WITH DT06-12X-XXXX PLUG
(X = A, B, C, D KEYS; XXXX: ALL MODIFICATIONS)
CONSULT FACTORY FOR MODIFICATIONS
- 2 PIN PLATING: GOLD OVER NICKLE OVER COPPER UNDERPLATE (Sn/Ni/Cu)
ENTIRE LENGTH OF PIN
(RoHS COMPLIANT)
- 1 MATERIAL: HOUSING - PA46 GF30 (SEE SHEETS 2 FOR COLORS)
PINS - COPPER ALLOY

NOTES:


THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN P. BURKE 12JUN2001	 TE Connectivity		
DIMENSIONS: INCHES [mm]		CHK J APOSTOL 25JUN2001			
TOLERANCES UNLESS OTHERWISE SPECIFIED: ±0.025 [0.64mm]		APVD S BEARD 25JUN2001	NAME 12 WAY RECEPTACLE 90 DEG FLANGELESS DTF SERIES		
		PRODUCT SPEC -	SIZE A3		
MATERIAL 		APPLICATION SPEC -	CAGE CODE 11139		
FINISH -		WEIGHT -	DRAWING NO G-DTF13-12PX-G003		
		CUSTOMER DRAWING	RESTRICTED TO -		
			SCALE 3:2		
			SHEET 1 OF 2		
			REV AI		

REVISIONS


P	LTR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET 1	-	-	-




DTF13-12PA-G003
COLOR: GREY




DTF13-12PB-G003
COLOR: BLACK



DTF13-12PC-G003
COLOR: GREEN



DTF13-12PD-G003
COLOR: BROWN

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN P. BURKE 12JUN2001	 TE Connectivity		
DIMENSIONS: INCHES [mm]		CHK J APOSTOL 25JUN2001			
TOLERANCES UNLESS OTHERWISE SPECIFIED: ±0.025 [0.64mm]		APVD S BEARD 25JUN2001	NAME 12 WAY RECEPTACLE 90 DEG FLANGELESS DTF SERIES		
		PRODUCT SPEC -	SIZE A3	CAGE CODE 111139	DRAWING NO G-DTF13-12PX-G003
MATERIAL 		APPLICATION SPEC -	RESTRICTED TO		
FINISH -		WEIGHT -	SCALE 2:1	SHEET 2 OF 2	REV A1
CUSTOMER DRAWING					

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[DTF13-12PA-G003](#)