



REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	J1	UPDATE FLAT WIDTH ECR-21-106386	05JUL2021	AFK	LS





SECTION A - A



Product Size	2.4	3.2	4.8	6.4	9.5	12	18	25	38
Minimum Sleeve Flattened Width	4.45 (.175)	5.84 (.230)	8.00 (.315)	10.67 (.420)	15.49 (.610)	20.45 (.805)	30.48 (1.200)	40.39 (1.590)	60.33 (2.375)
Nominal Sleeve Progression	12.70 (.500)	12.70 (.500)	12.70 (.500)	16.94 (.667)	25.40 (1.000)	29.64 (1.167)	42.34 (1.667)	50.80 (2.00)	71.96 (2.83)
"D" Minimum Supplied I.D.	2.39 (.094)	3.18 (.125)	4.75 (.187)	6.40 (.250)	9.53 (.375)	12.70 (.500)	19.05 (.750)	25.40 (1.00)	38.10 (1.50)
"d" Maximum Recovered I.D.	0.79 (.031)	1.07 (.042)	1.57 (.062)	2.11 (.083)	3.17 (.125)	4.22 (.166)	6.35 (.250)	8.46 (.333)	19.05 (.750)
"w" Recovered wall ±0.08 (.003)	0.51 (.023)	0.51 (.023)	0.58 (.023)	0.58 (.023)	0.61 (.024)	0.61 (.024)	0.61 (.024)	0.64 (.025)	0.64 (.025)

DIMENSIONS IN mm (inches)



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN AFK CHK — APVD LS PRODUCT SPEC RW-2519 APPLICATION SPEC 411-121008		08JAN2020 — 20JAN2020		 TE Connectivity									
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME		D-SCE									
		0 PLC ± —		PRODUCT SPEC		SIZE		CAGE CODE		DRAWING NO		RESTRICTED TO			
		1 PLC ± —		RW-2519											
		2 PLC ± —		APPLICATION SPEC											
		3 PLC ± —		411-121008											
		4 PLC ± —													
ANGLES ± —															
MATERIAL		FINISH		WEIGHT		A3		0198G		C=MCD160000		—			
CROSSLINKED POLYOLIFIN		—		VARIOUS											
CUSTOMER DRAWING										SCALE		SHEET		REV	
										NTS		1 OF 1		J1	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[EC1917-000](#)