



REVISIONS				
P	LTR	DESCRIPTION	DATE	APVD
	A	INITIAL	29MAY2015	DW CW
	A1	ECR-17-008664	17JUN2017	CH CW
	B	ECR-20-014876	06NOV2020	WOR CW



NOTES:
I. TECHNICAL CHARACTERISTICS:
HOOD MATERIAL: DIE CAST
ALUMINIUM ALLOY
SURFACE: POWDER COATED, GREY
DEGREE OF PROTECTION: IP65 (MATED)

注释：


1、技术参数：

上壳材料：	铝合金
表面处理：	灰色粉末喷涂
防护等级：	IP65（配合）

SCALE 3:5

TYPE 2: LOW CONSTRUCTION, TOP ENTRY
WITH STEEL DOUBLE LOCKING
OTHER SPEC REFER TO TYPE 1

类型2：低结构，顶出，带彩锌双扣，其它规格参照类型1




SCALE 3:5



TYPE 1: LOW CONSTRUCTION, SIDE ENTRY
WITH STEEL DOUBLE LOCKING

类型1：低结构，侧出，带彩锌双扣


T1260242132-000	H24B-TGB-M32	H24B HOOD, TOP ENTRY M32, METAL DOUBLE LOCKING, POWDER COATED, GREY H24B上壳, 顶出M32, 彩锌双扣, 灰色粉末喷涂	-	M32	TYPE 2 类型2
T1260242129-000	H24B-TGB-PG29	H24B HOOD, TOP ENTRY PG29, METAL DOUBLE LOCKING, POWDER COATED, GREY H24B上壳, 顶出PG29, 彩锌双扣, 灰色粉末喷涂	-	PG29	
T1260242125-000	H24B-TGB-M25	H24B HOOD, TOP ENTRY M25, METAL DOUBLE LOCKING, POWDER COATED, GREY H24B上壳, 顶出M25, 彩锌双扣, 灰色粉末喷涂	-	M25	
T1260242121-000	H24B-TGB-PG21	H24B HOOD, TOP ENTRY PG21, METAL DOUBLE LOCKING, POWDER COATED, GREY H24B上壳, 顶出PG21, 彩锌双扣, 灰色粉末喷涂	-	PG21	
T1260240000-000	H24B-TGB	H24B HOOD, NO ENTRY, METAL DOUBLE LOCKING, POWDER COATED, GREY H24B上壳, 无开孔, 彩锌双扣, 灰色粉末喷涂	-	-	TYPE 1 类型1
T1250242132-000	H24B-TSB-M32	H24B HOOD, SIDE ENTRY M32, METAL DOUBLE LOCKING, POWDER COATED, GREY H24B上壳, 侧出M32, 彩锌双扣, 灰色粉末喷涂	M32	-	
T1250242125-000	H24B-TSB-M25	H24B HOOD, SIDE ENTRY M25, METAL DOUBLE LOCKING, POWDER COATED, GREY H24B上壳, 侧出M25, 彩锌双扣, 灰色粉末喷涂	M25	-	
T1250242121-000	H24B-TSB-PG21	H24B HOOD, SIDE ENTRY PG21, METAL DOUBLE LOCKING, POWDER COATED, GREY H24B上壳, 侧出PG21, 彩锌双扣, 灰色粉末喷涂	PG21	-	
PART NUMBER 料号	PART DESCRIPTION 描述		PG/M THREAD 1 PG/M 螺纹孔1	PG/M THREAD 2 PG/M 螺纹孔2	TYPE 类型

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN DAVID.WANG	29MAY2015	 TE Connectivity			
		CHK CHRIS.WANG	29MAY2015				
		APVD XIANG.XU	29MAY2015				
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ±- 1 PLC ±- 2 PLC ±- 3 PLC ±- 4 PLC ±- ANGLES ±- FINISH		NAME H24B-TSB/TGB/TSBH/TGBH-M/PG			
				PRODUCT SPEC 108-137013			
MATERIAL - -				APPLICATION SPEC 114-137013			
		WEIGHT -		SIZE A2	CAGE CODE 00779	DRAWING NO C=T12X024XXXX000	RESTRICTED TO -
Customer Drawing				SCALE 1:1	SHEET 1 OF 2	REV B	

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET I	-	-	-



NOTES:
SEE SHEET 1



TYPE 3: HIGH CONSTRUCTION, SIDE ENTRY
WITH STEEL DOUBLE LOCKING
类型3: 高结构, 侧出, 带彩锌双扣

T1280242140-000	H10B-TGBH-M40	H24B HOOD, TOP ENTRY M40, METAL DOUBLE LOCKING, HIGH CONSTRUCTION, POWDER COATED, GREY H24B上壳,顶出M40,彩锌双扣,高结构,灰色粉末喷涂	-	M40	TYPE 4 类型4
T1280242132-000	H24B-TGBH-M32	H24B HOOD, TOP ENTRY M32, METAL DOUBLE LOCKING, HIGH CONSTRUCTION, POWDER COATED, GREY H24B上壳,顶出M32,彩锌双扣,高结构,灰色粉末喷涂	-	M32	
T1280242129-000	H24B-TGBH-PG29	H24B HOOD, TOP ENTRY PG29, METAL DOUBLE LOCKING, HIGH CONSTRUCTION, POWDER COATED, GREY H24B上壳,顶出PG29,彩锌双扣,高结构,灰色粉末喷涂	-	PG29	
T1280242125-000	H24B-TGBH-M25	H24B HOOD, TOP ENTRY M25, METAL DOUBLE LOCKING, HIGH CONSTRUCTION, POWDER COATED, GREY H24B上壳,顶出M25,彩锌双扣,高结构,灰色粉末喷涂	-	M25	
T1280242121-000	H24B-TGBH-PG21	H24B HOOD, TOP ENTRY PG21, METAL DOUBLE LOCKING, HIGH CONSTRUCTION, POWDER COATED, GREY H24B上壳,顶出PG21,彩锌双扣,高结构,灰色粉末喷涂	-	PG21	
T1270242140-000	H24B-TSBH-M40	H24B HOOD, SIDE ENTRY M40, METAL DOUBLE LOCKING, HIGH CONSTRUCTION, POWDER COATED, GREY H24B上壳,侧出M40,彩锌双扣,高结构,灰色粉末喷涂	M40	-	TYPE 3 类型3
T1270242132-000	H24B-TSBH-M32	H24B HOOD, SIDE ENTRY M32, METAL DOUBLE LOCKING, HIGH CONSTRUCTION, POWDER COATED, GREY H24B上壳,侧出M32,彩锌双扣,高结构,灰色粉末喷涂	M32	-	
T1270242129-000	H24B-TSBH-PG29	H24B HOOD, SIDE ENTRY PG29, METAL DOUBLE LOCKING, HIGH CONSTRUCTION, POWDER COATED, GREY H24B上壳,侧出PG29,彩锌双扣,高结构,灰色粉末喷涂	PG29	-	
T1270242121-000	H24B-TSBH-PG21	H24B HOOD, SIDE ENTRY PG21, METAL DOUBLE LOCKING, HIGH CONSTRUCTION, POWDER COATED, GREY H24B上壳,侧出PG21,彩锌双扣,高结构,灰色粉末喷涂	PG21	-	
PART NUMBER 料号	PART DESCRIPTION 描述		PG/M THREAD 1 PG/M 螺纹孔1	PG/M THREAD 2 PG/M 螺纹孔2	TYPE 类型

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 29MAY2015 DAVID.WANG CHK 29MAY2015 CHRIS.WANG APVD 29MAY2015 XIANG.XU		 TE Connectivity	
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ±. 1 PLC ±. 2 PLC ±. 3 PLC ±. 4 PLC ±. ANGLES ±. FINISH		NAME H24B-TSB/TGB/TSBH/TGBH-M/PG	
		PRODUCT SPEC 108-137013 APPLICATION SPEC 114-137013		SIZE A2	
MATERIAL - -		WEIGHT - Customer Drawing		CAGE CODE 00779	
				DRAWING NO C-T12X024XXXX000	
				RESTRICTED TO -	
				SCALE 1:1	
				SHEET 2 OF 2	
				REV B	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[T1280242121-000](#)