




REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	INITIAL RELEASE	17JUN2015	DL	CW
	A1	ECR-18-019196	11DEC2018	WQR	CW
	B	ECR-20-014876	23JUL2021	WQR	CW



NOTES:
1. TECHNICAL CHARACTERISTICS:
BODY MATERIAL: DIE CAST ALUMINIUM ALLOY
SURFACE TREATMENT: POWDER-COATED, GRAY
DEGREE OF PROTECTION: IP65 (MATED)

注 释:

1. 技术参数:	
主体材料:	铝合金
表面处理:	粉末喷涂, 灰色
防护等级:	IP65(配合)





TYPE I: HIGH CONSTRUCTION + PLASTIC PROTECTION COVER
类型 I: 高结构+带塑料保护盖

T1490240121-000	H24B-SDRH-B0-PG21	H24B HOUSING,SURFACE MOUNTED, 4 EAR,PG21,HIGH CONSTRUCTION, PLASTIC PROTECTION COVER,POWDER COATED,GREY H24B外壳,表面安装,4耳,PG21,高结构,带塑料保护盖,灰色粉末喷涂	PG21	-	TYPE I 类型 I	
T1490240125-000	H24B-SDRH-B0-M25	H24B HOUSING,SURFACE MOUNTED, 4 EAR,M25,HIGH CONSTRUCTION, PLASTIC PROTECTION COVER,POWDER COATED,GREY H24B外壳,表面安装,4耳,M25,高结构,带塑料保护盖,灰色粉末喷涂	M25	-		
T1490240129-000	H24B-SDRH-B0-PG29	H24B HOUSING,SURFACE MOUNTED, 4 EAR,PG29,HIGH CONSTRUCTION, PLASTIC PROTECTION COVER,POWDER COATED,GREY H24B外壳,表面安装,4耳,PG29,高结构,带塑料保护盖,灰色粉末喷涂	PG29	-		
T1490240132-000	H24B-SDRH-B0-M32	H24B HOUSING,SURFACE MOUNTED, 4 EAR,M32,HIGH CONSTRUCTION, PLASTIC PROTECTION COVER,POWDER COATED,GREY H24B外壳,表面安装,4耳,M32,高结构,带塑料保护盖,灰色粉末喷涂	M32	-		
T1490240221-000	H24B-SDRH-B0-2PG21	H24B HOUSING,SURFACE MOUNTED, 4 EAR,2PG21,HIGH CONSTRUCTION, PLASTIC PROTECTION COVER,POWDER COATED,GREY H24B外壳,表面安装,4耳,2PG21,高结构,带塑料保护盖,灰色粉末喷涂	PG21	PG21		
T1490240225-000	H24B-SDRH-B0-2M25	H24B HOUSING,SURFACE MOUNTED, 4 EAR,2M25,HIGH CONSTRUCTION, PLASTIC PROTECTION COVER,POWDER COATED,GREY H24B外壳,表面安装,4耳,2M25,高结构,带塑料保护盖,灰色粉末喷涂	M25	M25		
T1490240229-000	H24B-SDRH-B0-2PG29	H24B HOUSING,SURFACE MOUNTED, 4 EAR,2PG29,HIGH CONSTRUCTION, PLASTIC PROTECTION COVER,POWDER COATED,GREY H24B外壳,表面安装,4耳,2PG29,高结构,带塑料保护盖,灰色粉末喷涂	PG29	PG29		
T1490240232-000	H24B-SDRH-B0-2M32	H24B HOUSING,SURFACE MOUNTED, 4 EAR,2M32,HIGH CONSTRUCTION, PLASTIC PROTECTION COVER,POWDER COATED,GREY H24B外壳,表面安装,4耳,2M32,高结构,带塑料保护盖,灰色粉末喷涂	M32	M32		
PART NUMBER 料号	DESCRIPTION 描述			1G1	1G2	TYPE 类型

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN DAVID LI 17JUN2015 CHK CHRIS WANG 17JUN2015 APVD XU XIANG 17JUN2015		 TE Connectivity	
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME	
		0 PLC ±- 1 PLC ±- 2 PLC ±- 3 PLC ±- 4 PLC ±- ANGLES ±-		H24B-SDRH/SDRHM-BO-PG/M	
		PRODUCT SPEC		SIZE CAGE CODE DRAWING NO RESTRICTED TO A2 - C-T149024XXXX000	
		APPLICATION SPEC 108-137013 114-137013			
MATERIAL		FINISH		WEIGHT	
-		-		-	
-		-		-	
CUSTOMER DRAWING				SCALE	REV
				3:4	B

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET I	-	-	-



注释：
见 表 |

T1490241121-000	H24B-SDRHM-BO-PG21	H24B HOUSING,SURFACE MOUNTED, 4 EAR,PG21,HIGH CONSTRUCTION, METAL PROTECTION COVER,POWDER COATED,GREY H24B下壳,表面安装,4耳,PG21,高结构,合金属保护罩,灰色粉末喷涂	PG21	-	TYPE 2 类型 2	
T1490241129-000	H24B-SDRHM-BO-PG29	H24B HOUSING,SURFACE MOUNTED, 4 EAR,PG29,HIGH CONSTRUCTION, METAL PROTECTION COVER,POWDER COATED,GREY H24B下壳,表面安装,4耳,PG29,高结构,合金属保护罩,灰色粉末喷涂	PG29	-		
T1490241132-000	H24B-SDRHM-BO-M32	H24B HOUSING,SURFACE MOUNTED, 4 EAR,M32,HIGH CONSTRUCTION, METAL PROTECTION COVER,POWDER COATED,GREY H24B下壳,表面安装,4耳,M32,高结构,合金属保护罩,灰色粉末喷涂	M32	-		
T1490241221-000	H24B-SDRHM-BO-2PG21	H24B HOUSING,SURFACE MOUNTED, 4 EAR,2PG21,HIGH CONSTRUCTION, METAL PROTECTION COVER,POWDER COATED,GREY H24B下壳,表面安装,4耳,2PG21,高结构,合金属保护罩,灰色粉末喷涂	PG21	PG21		
T1490241229-000	H24B-SDRHM-BO-2PG29	H24B HOUSING,SURFACE MOUNTED, 4 EAR,2PG29,HIGH CONSTRUCTION, METAL PROTECTION COVER,POWDER COATED,GREY H24B下壳,表面安装,4耳,2PG29,高结构,合金属保护罩,灰色粉末喷涂	PG29	PG29		
T1490241232-000	H24B-SDRHM-BO-2M32	H24B HOUSING,SURFACE MOUNTED, 4 EAR,2M32,HIGH CONSTRUCTION, METAL PROTECTION COVER,POWDER COATED,GREY H24B下壳,表面安装,4耳,2M32,高结构,合金属保护罩,灰色粉末喷涂	M32	M32		
PART NUMBER 料号	DESCRIPTION 描述			IG1	IG2	TYPE 类型

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN DAVID LI 17JUN2015 CHK CHRIS WANG 17JUN2015 APVD XU XIANG 17JUN2015		 TE Connectivity	
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME	
		0 PLC ±- 1 PLC ±- 2 PLC ±- 3 PLC ±- 4 PLC ±- ANGLES ±-		H24B-SDRH/SDRHM-BO-PG/M	
		PRODUCT SPEC		SIZE CAGE CODE DRAWING NO RESTRICTED TO A2 - C-T149024XXXX000	
		APPLICATION SPEC 108-137013 114-137013			
MATERIAL		FINISH		WEIGHT	
-		-		-	
-		-		-	
CUSTOMER DRAWING				SCALE	REV
				3:4	B

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[T1490240221-000](#)