


REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	INITIAL RELEASE	17JUN2015	DL	CW
	A1	ECR-18-019196	11DEC2018	WQR	CW
	B	ECR-20-014876	23JUL2021	WQR	CW



NOTES:
1. TECHNICAL CHARACTERISTICS:
BODY MATERIAL: DIE CAST ALUMINIUM ALLOY
SURFACE TREATMENT: POWDER-COATED, GRAY
DEGREE OF PROTECTION: IP65 (MATED)



注 释:

1. 技术参数:

主体材料: 铝合金

表面处理: 粉末喷涂, 灰色




防护等级: IP65(配合)



TYPE 1: HIGH CONSTRUCTION + PLASTIC PROTECTON COVER
类型 1: 高结构+带塑料保护盖

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN DAVID LI 17JUN2015 CHK CHRIS WANG 17JUN2015 APVD XU XIANG 17JUN2015		 TE Connectivity	
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME	
		PRODUCT SPEC		H24B-SDRH/SDRHM-BO-PG/M	
		108-137013			
		APPLICATION SPEC			
MATERIAL		114-137013		SIZE	CAGE CODE
-		WEIGHT		A2	-
-		CUSTOMER DRAWING		DRAWING NO	
				C-T149024XXXX000	
				SCALE	SHEET
				3:4	1 OF 2
				REV	B


REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET I	-	-	-



NOTES:
SEE SHEET 1

注释：
见 表 1

T1490241121-000	H24B-SDRHM-BO-PG21	H24B HOUSING,SURFACE MOUNTED, 4 EAR,PG21,HIGH CONSTRUCTION, METAL PROTECTION COVER,POWDER COATED,GREY H24B下壳,表面安装,4耳,PG21,高结构,合金属保护罩,灰色粉末喷涂	PG21	-	TYPE 2 类型 2	
T1490241129-000	H24B-SDRHM-BO-PG29	H24B HOUSING,SURFACE MOUNTED, 4 EAR,PG29,HIGH CONSTRUCTION, METAL PROTECTION COVER,POWDER COATED,GREY H24B下壳,表面安装,4耳,PG29,高结构,合金属保护罩,灰色粉末喷涂	PG29	-		
T1490241132-000	H24B-SDRHM-BO-M32	H24B HOUSING,SURFACE MOUNTED, 4 EAR,M32,HIGH CONSTRUCTION, METAL PROTECTION COVER,POWDER COATED,GREY H24B下壳,表面安装,4耳,M32,高结构,合金属保护罩,灰色粉末喷涂	M32	-		
T1490241221-000	H24B-SDRHM-BO-2PG21	H24B HOUSING,SURFACE MOUNTED, 4 EAR,2PG21,HIGH CONSTRUCTION, METAL PROTECTION COVER,POWDER COATED,GREY H24B下壳,表面安装,4耳,2PG21,高结构,合金属保护罩,灰色粉末喷涂	PG21	PG21		
T1490241229-000	H24B-SDRHM-BO-2PG29	H24B HOUSING,SURFACE MOUNTED, 4 EAR,2PG29,HIGH CONSTRUCTION, METAL PROTECTION COVER,POWDER COATED,GREY H24B下壳,表面安装,4耳,2PG29,高结构,合金属保护罩,灰色粉末喷涂	PG29	PG29		
T1490241232-000	H24B-SDRHM-BO-2M32	H24B HOUSING,SURFACE MOUNTED, 4 EAR,2M32,HIGH CONSTRUCTION, METAL PROTECTION COVER,POWDER COATED,GREY H24B下壳,表面安装,4耳,2M32,高结构,合金属保护罩,灰色粉末喷涂	M32	M32		
PART NUMBER 料号	DESCRIPTION 描述			IG1	IG2	TYPE 类型



TYPE 2: HIGH CONSTRUCTION + METAL PROTECTION COVER
OTHER SPEC REFER TO TYPE 1

类型 2: 高结构+带金属保护盖保护盖
其余规范参考类型 1

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 17JUN2015 CHK DAVID LI 17JUN2015 CHRIS WANG APVD XU XIANG 17JUN2015		 TE Connectivity	
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME	
		0 PLC ± 1 PLC ± 2 PLC ± 3 PLC ± 4 PLC ± ANGLES ±		H24B-SDRH/SDRHM-BO-PG/M	
		PRODUCT SPEC			
		APPLICATION SPEC			
MATERIAL		FINISH		SIZE	CAGE CODE
-		-		A2	-
-		-		DRAWING NO	
		WEIGHT		C=TI49024XXXX000	
		CUSTOMER DRAWING		RESTRICTED TO	
				SCALE	REV
				3:4	B
				SHEET	2 OF 2

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[T1490240132-000](#)