







THIS DRAWING IS UNPUBLISHED.	RELEASED FOR PUBLICATION	20
© COPYRIGHT 20	BY -	ALL RIGHTS RESERVED.

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET I	-	-	-






TYPE 4: H24B HOUSING,SURFACE MOUNTED,METAL SINGLE LOCKING,SIDE ENTRY 2M25,
BOTTOM ENTRY M20+PLASTIC PROTECTION COVER
OTHER SPEC REFER TO TYPE 2

类型4: H24B下壳,表面安装,彩锌单扣,侧出2M25,底出M20+带塑料保护盖
其余规范参考类型2

T1610243121-000	H24B-SGR-LB-PG21	H24B HOUSING,SURFACE MOUNTED, METAL SINGLE LOCKING,PG21,POWDER COATED,GREY H24B下壳,表面安装,彩锌单扣,PG21,灰色粉末喷涂	PG21	-	TYPE 1 类型 1	
T1610243125-000	H24B-SGR-LB-M25	H24B HOUSING,SURFACE MOUNTED, METAL SINGLE LOCKING,M25,POWDER COATED,GREY H24B下壳,表面安装,彩锌单扣,M25,灰色粉末喷涂	M25	-		
T1610243221-000	H24B-SGR-LB-2PG21	H24B HOUSING,SURFACE MOUNTED, METAL SINGLE LOCKING,2PG21,POWDER COATED,GREY H24B下壳,表面安装,彩锌单扣,2PG21,灰色粉末喷涂	PG21	PG21		
T1610243225-000	H24B-SGR-LB-2M25	H24B HOUSING,SURFACE MOUNTED, METAL SINGLE LOCKING,2M25,POWDER COATED,GREY H24B下壳,表面安装,彩锌单扣,2M25,灰色粉末喷涂	M25	M25		
T1620243121-000	H24B-SDR-LB-PG21	H24B HOUSING,SURFACE MOUNTED,METAL SINGLE LOCKING,PG21, PLASTIC PROTECTION COVER,POWDER COATED,GREY H24B下壳,表面安装,彩锌单扣,PG21,带塑料保护盖,灰色粉末喷涂	PG21	-	TYPE 2 类型 2	
T1620243125-000	H24B-SDR-LB-M25	H24B HOUSING,SURFACE MOUNTED,METAL SINGLE LOCKING,M25, PLASTIC PROTECTION COVER,POWDER COATED,GREY H24B下壳,表面安装,彩锌单扣,M25,带塑料保护盖,灰色粉末喷涂	M25	-		
T1620243221-000	H24B-SDR-LB-2PG21	H24B HOUSING,SURFACE MOUNTED,METAL SINGLE LOCKING,2PG21, PLASTIC PROTECTION COVER,POWDER COATED,GREY H24B下壳,表面安装,彩锌单扣,2PG21,带塑料保护盖,灰色粉末喷涂	PG21	PG21		
T1620243225-000	H24B-SDR-LB-2M25	H24B HOUSING,SURFACE MOUNTED,METAL SINGLE LOCKING,2M25, PLASTIC PROTECTION COVER,POWDER COATED,GREY H24B下壳,表面安装,彩锌单扣,2M25,带塑料保护盖,灰色粉末喷涂	M25	M25		
T1620243421-000	H24B-SDRM-LB-PG21	H24B HOUSING,SURFACE MOUNTED,METAL SINGLE LOCKING, PG21,METAL PROTECTION COVER,POWDER COATED,GREY H24B下壳,表面安装,彩锌单扣,PG21,带金属保护盖,灰色粉末喷涂	PG21	-	TYPE 3 类型 3	
T1620243425-000	H24B-SDRM-LB-M25	H24B HOUSING,SURFACE MOUNTED,METAL SINGLE LOCKING, M25,METAL PROTECTION COVER,POWDER COATED,GREY H24B下壳,表面安装,彩锌单扣,M25,带金属保护盖,灰色粉末喷涂	M25	-		
T1620243321-000	H24B-SDRM-LB-2PG21	H24B HOUSING,SURFACE MOUNTED,METAL SINGLE LOCKING, 2PG21,METAL PROTECTION COVER,POWDER COATED,GREY H24B下壳,表面安装,彩锌单扣,2PG21,带金属保护盖,灰色粉末喷涂	PG21	PG21		
T1620243325-000	H24B-SDRM-LB-2M25	H24B HOUSING,SURFACE MOUNTED,METAL SINGLE LOCKING, 2M25,METAL PROTECTION COVER,POWDER COATED,GREY H24B下壳,表面安装,彩锌单扣,2M25,带金属保护盖,灰色粉末喷涂	M25	M25		
T1620242520-000	H24B-SDR-LB-2M25/M20	H24B HOUSING,SURFACE MOUNTED,METAL SINGLE LOCKING,SIDE ENTRY 2M25, BOTTOM ENTRY M20,PLASTIC PROTECTION COVER,POWDER COATED,GREY H24B下壳,表面安装,彩锌单扣,侧出2M25,底出M20,带塑料保护盖,灰色粉末喷涂	M25	M25	TYPE 4 类型 4	
PART NUMBER 料 号	DESCRIPTION 描 述			IG1	IG2	TYPE 类 型

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 02JUL2015 CHK DAVID LI 02JUL2015 CHRIS WANG APVD XU XIANG 02JUL2015		 TE Connectivity	
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ±. 1 PLC ±. 2 PLC ±. 3 PLC ±. 4 PLC ±. ANGLES ±.		NAME H24B-SGR/SDR/SDRM/SGRH/SDRH/ SDRHM-LB-PG/M	
		PRODUCT SPEC 108-137013 APPLICATION SPEC 114-137013		SIZE A2	
MATERIAL - -		FINISH - -		CAGE CODE -	
		WEIGHT -		DRAWING NO C-T16X0243XXXX00	
		Customer Drawing		SCALE 1:2 SHEET 2 OF 4 REV B	

P	LTR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET 1	-	-	-



TYPE 5: H24B HOUSING,SURFACE MOUNTED,METAL SINGLE LOCKING,HIGH CONSTRUCTION

类型5: H24B下壳,表面安装,彩锌单扣,高结构

TYPE 6: H24B HOUSING,SURFACE MOUNTED,METAL SINGLE LOCKING,HIGH CONSTRUCTION+PLASTIC PROTECTION COVER

OTHER SPEC REFER TO TYPE 5

类型6: H24B下壳,表面安装,彩锌单扣,高结构+带塑料保护盖

其余规范参考类型5

TYPE 7: H24B HOUSING,SURFACE MOUNTED,METAL SINGLE LOCKING,HIGH CONSTRUCTION+METAL PROTECTION COVER

OTHER SPEC REFER TO TYPE 5

类型7: H24B下壳,表面安装,彩锌单扣,高结构+带金属保护盖

其余规范参考类型5

TYPE 8: H24B HOUSING,SURFACE MOUNTED,METAL SINGLE LOCKING,HIGH CONSTRUCTION+METAL PROTECTION COVER

OTHER SPEC REFER TO TYPE 5

类型8: H24B下壳,表面安装,彩锌单扣,高结构+带金属保护盖

其余规范参考类型5

TYPE 9: H24B HOUSING,SURFACE MOUNTED,METAL SINGLE LOCKING,HIGH CONSTRUCTION+METAL PROTECTION COVER

OTHER SPEC REFER TO TYPE 5

类型9: H24B下壳,表面安装,彩锌单扣,高结构+带金属保护盖

其余规范参考类型5

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN DAVID LI 02JUL2015

CHK CHRIS WANG 02JUL2015

APVD XU XIANG 02JUL2015

PRODUCT SPEC

APPLICATION SPEC

114-137013

WEIGHT

-

Customer Drawing

TE Connectivity

H24B-SGR/SDR/SDRM/SGRH/SDRH/SDRHM-LB-PG/M

SIZE A2

CAGE CODE -

DRAWING NO C-T16X0243XXXX00

RESTRICTED TO -

SCALE 1:2

SHEET 3 OF 4

REV B

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

20

© COPYRIGHT 20

BY -

ALL RIGHTS RESERVED.


REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
-		SEE SHEET 1	-	-	-

T1650243121-000	H24B-SGRH-LB-PG21	H24B HOUSING,SURFACE MOUNTED,METAL SINGLE LOCKING,PG21,HIGH CONSTRUCTION,POWDER COATED,GREY H24B下壳,表面安装,彩锌单扣,PG21,高结构,灰色粉末喷涂	PG21	-	TYPE 5 类 型 5
T1650243125-000	H24B-SGRH-LB-M25	H24B HOUSING,SURFACE MOUNTED,METAL SINGLE LOCKING,M25,HIGH CONSTRUCTION,POWDER COATED,GREY H24B下壳,表面安装,彩锌单扣,M25,高结构,灰色粉末喷涂	M25	-	
T1650243129-000	H24B-SGRH-LB-PG29	H24B HOUSING,SURFACE MOUNTED,METAL SINGLE LOCKING,PG29,HIGH CONSTRUCTION,POWDER COATED,GREY H24B下壳,表面安装,彩锌单扣,PG29,高结构,灰色粉末喷涂	PG29	-	
T1650243132-000	H24B-SGRH-LB-M32	H24B HOUSING,SURFACE MOUNTED,METAL SINGLE LOCKING,M32,HIGH CONSTRUCTION,POWDER COATED,GREY H24B下壳,表面安装,彩锌单扣,M32,高结构,灰色粉末喷涂	M32	-	
T1650243221-000	H24B-SGRH-LB-2PG21	H24B HOUSING,SURFACE MOUNTED,METAL SINGLE LOCKING,2PG21,HIGH CONSTRUCTION,POWDER COATED,GREY H24B下壳,表面安装,彩锌单扣,2PG21,高结构,灰色粉末喷涂	PG21	PG21	
T1650243229-000	H24B-SGRH-LB-2PG29	H24B HOUSING,SURFACE MOUNTED,METAL SINGLE LOCKING,2PG29,HIGH CONSTRUCTION,POWDER COATED,GREY H24B下壳,表面安装,彩锌单扣,2PG29,高结构,灰色粉末喷涂	PG29	PG29	
T1650243232-000	H24B-SGRH-LB-2M32	H24B HOUSING,SURFACE MOUNTED,METAL SINGLE LOCKING,2M32,HIGH CONSTRUCTION,POWDER COATED,GREY H24B下壳,表面安装,彩锌单扣,2M32,高结构,灰色粉末喷涂	M32	M32	TYPE 6 类 型 6
T1660243121-000	H24B-SDRH-LB-PG21	H24B HOUSING,SURFACE MOUNTED,METAL SINGLE LOCKING,PG21,HIGH CONSTRUCTION,PLASTIC PROTECTION COVER,POWDER COATED,GREY H24B下壳,表面安装,彩锌单扣,PG21,高结构,带塑料保护盖,灰色粉末喷涂	PG21	-	
T1660243129-000	H24B-SDRH-LB-PG29	H24B HOUSING,SURFACE MOUNTED,METAL SINGLE LOCKING,PG29,HIGH CONSTRUCTION,PLASTIC PROTECTION COVER,POWDER COATED,GREY H24B下壳,表面安装,彩锌单扣,PG29,高结构,带塑料保护盖,灰色粉末喷涂	PG29	-	
T1660243132-000	H24B-SDRH-LB-M32	H24B HOUSING,SURFACE MOUNTED,METAL SINGLE LOCKING,M32,HIGH CONSTRUCTION,PLASTIC PROTECTION COVER,POWDER COATED,GREY H24B下壳,表面安装,彩锌单扣,M32,高结构,带塑料保护盖,灰色粉末喷涂	M32	-	
T1660243221-000	H24B-SDRH-LB-2PG21	H24B HOUSING,SURFACE MOUNTED,METAL SINGLE LOCKING,2PG21,HIGH CONSTRUCTION,PLASTIC PROTECTION COVER,POWDER COATED,GREY H24B下壳,表面安装,彩锌单扣,2PG21,高结构,带塑料保护盖,灰色粉末喷涂	PG21	PG21	
T1660243229-000	H24B-SDRH-LB-2PG29	H24B HOUSING,SURFACE MOUNTED,METAL SINGLE LOCKING,2PG29,HIGH CONSTRUCTION,PLASTIC PROTECTION COVER,POWDER COATED,GREY H24B下壳,表面安装,彩锌单扣,2PG29,高结构,带塑料保护盖,灰色粉末喷涂	PG29	PG29	
T1660243232-000	H24B-SDRH-LB-2M32	H24B HOUSING,SURFACE MOUNTED,METAL SINGLE LOCKING,2M32,HIGH CONSTRUCTION,PLASTIC PROTECTION COVER,POWDER COATED,GREY H24B下壳,表面安装,彩锌单扣,2M32,高结构,带塑料保护盖,灰色粉末喷涂	M32	M32	TYPE 7 类 型 7
T1660243121-100	H24B-SDRHM-LB-PG21	H24B HOUSING,SURFACE MOUNTED,METAL SINGLE LOCKING,PG21,HIGH CONSTRUCTION,METAL PROTECTION COVER,POWDER COATED,GREY H24B下壳,表面安装,彩锌单扣,PG21,高结构,带金属保护盖,灰色粉末喷涂	PG21	-	
T1660243129-100	H24B-SDRHM-LB-PG29	H24B HOUSING,SURFACE MOUNTED,METAL SINGLE LOCKING,PG29,HIGH CONSTRUCTION,METAL PROTECTION COVER,POWDER COATED,GREY H24B下壳,表面安装,彩锌单扣,PG29,高结构,带金属保护盖,灰色粉末喷涂	PG29	-	
T1660243132-100	H24B-SDRHM-LB-M32	H24B HOUSING,SURFACE MOUNTED,METAL SINGLE LOCKING,M32,HIGH CONSTRUCTION,METAL PROTECTION COVER,POWDER COATED,GREY H24B下壳,表面安装,彩锌单扣,M32,高结构,带金属保护盖,灰色粉末喷涂	M32	-	
T1660243221-100	H24B-SDRHM-LB-2PG21	H24B HOUSING,SURFACE MOUNTED,METAL SINGLE LOCKING,2PG21,HIGH CONSTRUCTION,METAL PROTECTION COVER,POWDER COATED,GREY H24B下壳,表面安装,彩锌单扣,2PG21,高结构,带金属保护盖,灰色粉末喷涂	PG21	PG21	
T1660243229-100	H24B-SDRHM-LB-2PG29	H24B HOUSING,SURFACE MOUNTED,METAL SINGLE LOCKING,2PG29,HIGH CONSTRUCTION,METAL PROTECTION COVER,POWDER COATED,GREY H24B下壳,表面安装,彩锌单扣,2PG29,高结构,带金属保护盖,灰色粉末喷涂	PG29	PG29	
T1660243232-100	H24B-SDRHM-LB-2M32	H24B HOUSING,SURFACE MOUNTED,METAL SINGLE LOCKING,2M32,HIGH CONSTRUCTION,METAL PROTECTION COVER,POWDER COATED,GREY H24B下壳,表面安装,彩锌单扣,2M32,高结构,带金属保护盖,灰色粉末喷涂	M32	M32	
PART NUMBER 料 号	DESCRIPTION 描 述		IG1	IG2	TYPE 类 型

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm



TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ±-

1 PLC ±

2 PLC ±

3 PLC ±-

4 PLC ±-

ANGLES ±-

FINISH -

-

DWN DAVID LI 02JUL2015

CHK CHRIS WANG 02JUL2015

APVD XU XIANG 02JUL2015

PRODUCT SPEC 108-137013

APPLICATION SPEC 114-137013

WEIGHT -

Customer Drawing

TE Connectivity

NAMEH24B-SGR/SDR/SDRM/SGRH/SDRH/SDRHM-LB-PG/M

SIZEA2

CAGE CODE-

DRAWING NO. ©T16X0243XXXX00

RESTRICTED TO-

SCALE1:2SHEET4OF4REV B

1471-9 (3/13)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[T1620243325-000](#)