



P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	INITIAL RELEASE	02JUL2015	DL	CW
	AI	ECR-18-019196	02JAN2019	WOR	CW
	B	ECR-20-014876	27JUL2021	WOR	CW



TYPE 1: H24B HOUSING, SURFACE MOUNTED, METAL SINGLE LOCKING.
类型1: H24B下壳, 表面安装, 彩锌单扣.

TYPE 2: H24B HOUSING, SURFACE MOUNTED, METAL SINGLE LOCKING+PLASTIC PROTECTION COVER
OTHER SPEC REFER TO TYPE 1
类型2: H24B下壳, 表面安装, 彩锌单扣+带塑料保护盖
其余规范参考类型1



TYPE 3: H24B HOUSING, SURFACE MOUNTED, METAL SINGLE LOCKING+METAL PROTECTION COVER
OTHER SPEC REFER TO TYPE 1
类型3: H24B下壳, 表面安装, 彩锌单扣+带金属保护盖
其余规范参考类型1






NOTES:
1. TECHNICAL CHARACTERISTICS:
BODY MATERIAL: DIE CAST ALUMINIUM ALLOY
SURFACE TREATMENT: POWDER-COATED, GRAY
DEGREE OF PROTECTION: IP65 (MATED)

注释:
1. 技术参数:
主体材料: 铝合金
表面处理: 粉末喷涂, 灰色
防护等级: IP65(配合)

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN DAVID LI 02JUL2015	TE Connectivity		
DIMENSIONS:		CHK CHRIS WANG 02JUL2015			
mm	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD XU XIANG 02JUL2015	NAME H24B-SGR/SDR/SDRM/SGRH/SDRH/SDRHM-LB-PG/M		
	0 PLC ±	PRODUCT SPEC 108-137013	SIZE A2	CAGE CODE -	DRAWING NO C-T16X0243XXXX00
	1 PLC ±	APPLICATION SPEC 114-137013	RESTRICTED TO -		
	2 PLC ±	WEIGHT -			
	3 PLC ±	Customer Drawing			
	4 PLC ±				
	ANGLES ±				
MATERIAL	FINISH				
-	-				
-	-				

THIS DRAWING IS UNPUBLISHED.	RELEASED FOR PUBLICATION	20
(C) COPYRIGHT 20	BY -	ALL RIGHTS RESERVED.

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET I	-	-	-






TYPE 4: H24B HOUSING,SURFACE MOUNTED,METAL SINGLE LOCKING,SIDE ENTRY 2M25,
BOTTOM ENTRY M20+PLASTIC PROTECTION COVER
OTHER SPEC REFER TO TYPE 2

类型4: H24B下壳,表面安装,彩锌单扣,侧出2M25,底出M20+带塑料保护盖
其余规范参考类型2

T1610243121-000	H24B-SGR-LB-PG21	H24B HOUSING,SURFACE MOUNTED, METAL SINGLE LOCKING,PG21,POWDER COATED,GREY H24B下壳,表面安装,彩锌单扣,PG21,灰色粉末喷涂	PG21	-	TYPE 1 类 型 1	
T1610243125-000	H24B-SGR-LB-M25	H24B HOUSING,SURFACE MOUNTED, METAL SINGLE LOCKING,M25,POWDER COATED,GREY H24B下壳,表面安装,彩锌单扣,M25,灰色粉末喷涂	M25	-		
T1610243221-000	H24B-SGR-LB-2PG21	H24B HOUSING,SURFACE MOUNTED, METAL SINGLE LOCKING,2PG21,POWDER COATED,GREY H24B下壳,表面安装,彩锌单扣,2PG21,灰色粉末喷涂	PG21	PG21		
T1610243225-000	H24B-SGR-LB-2M25	H24B HOUSING,SURFACE MOUNTED, METAL SINGLE LOCKING,2M25,POWDER COATED,GREY H24B下壳,表面安装,彩锌单扣,2M25,灰色粉末喷涂	M25	M25		
T1620243121-000	H24B-SDR-LB-PG21	H24B HOUSING,SURFACE MOUNTED,METAL SINGLE LOCKING,PG21, PLASTIC PROTECTION COVER,POWDER COATED,GREY H24B下壳,表面安装,彩锌单扣,PG21,带塑料保护盖,灰色粉末喷涂	PG21	-	TYPE 2 类 型 2	
T1620243125-000	H24B-SDR-LB-M25	H24B HOUSING,SURFACE MOUNTED,METAL SINGLE LOCKING,M25, PLASTIC PROTECTION COVER,POWDER COATED,GREY H24B下壳,表面安装,彩锌单扣,M25,带塑料保护盖,灰色粉末喷涂	M25	-		
T1620243221-000	H24B-SDR-LB-2PG21	H24B HOUSING,SURFACE MOUNTED,METAL SINGLE LOCKING,2PG21, PLASTIC PROTECTION COVER,POWDER COATED,GREY H24B下壳,表面安装,彩锌单扣,2PG21,带塑料保护盖,灰色粉末喷涂	PG21	PG21		
T1620243225-000	H24B-SDR-LB-2M25	H24B HOUSING,SURFACE MOUNTED,METAL SINGLE LOCKING,2M25, PLASTIC PROTECTION COVER,POWDER COATED,GREY H24B下壳,表面安装,彩锌单扣,2M25,带塑料保护盖,灰色粉末喷涂	M25	M25		
T1620243421-000	H24B-SDRM-LB-PG21	H24B HOUSING,SURFACE MOUNTED,METAL SINGLE LOCKING, PG21,METAL PROTECTION COVER,POWDER COATED,GREY H24B下壳,表面安装,彩锌单扣,PG21,带金属保护盖,灰色粉末喷涂	PG21	-	TYPE 3 类 型 3	
T1620243425-000	H24B-SDRM-LB-M25	H24B HOUSING,SURFACE MOUNTED,METAL SINGLE LOCKING, M25,METAL PROTECTION COVER,POWDER COATED,GREY H24B下壳,表面安装,彩锌单扣,M25,带金属保护盖,灰色粉末喷涂	M25	-		
T1620243321-000	H24B-SDRM-LB-2PG21	H24B HOUSING,SURFACE MOUNTED,METAL SINGLE LOCKING, 2PG21,METAL PROTECTION COVER,POWDER COATED,GREY H24B下壳,表面安装,彩锌单扣,2PG21,带金属保护盖,灰色粉末喷涂	PG21	PG21		
T1620243325-000	H24B-SDRM-LB-2M25	H24B HOUSING,SURFACE MOUNTED,METAL SINGLE LOCKING, 2M25,METAL PROTECTION COVER,POWDER COATED,GREY H24B下壳,表面安装,彩锌单扣,2M25,带金属保护盖,灰色粉末喷涂	M25	M25		
T1620242520-000	H24B-SDR-LB-2M25/M20	H24B HOUSING,SURFACE MOUNTED,METAL SINGLE LOCKING,SIDE ENTRY 2M25, BOTTOM ENTRY M20,PLASTIC PROTECTION COVER,POWDER COATED,GREY H24B下壳,表面安装,彩锌单扣,侧出2M25,底出M20,带塑料保护盖,灰色粉末喷涂	M25	M25	TYPE 4 类 型 4	
PART NUMBER 料 号	DESCRIPTION 描 述			IG1	IG2	TYPE 类 型

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 02JUL2015 CHK DAVID LI 02JUL2015 CHRIS WANG APVD XU XIANG 02JUL2015		 TE Connectivity			
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ±. 1 PLC ±. 2 PLC ±. 3 PLC ±. 4 PLC ±. ANGLES ±. FINISH		NAME H24B-SGR/SDR/SDRM/SGRH/SDRH/ SDRHM-LB-PG/M			
		PRODUCT SPEC 108-137013 APPLICATION SPEC 114-137013		SIZE A2		CAGE CODE -	
MATERIAL - -		WEIGHT - Customer Drawing		DRAWING NO C-T16X0243XXXX00		RESTRICTED TO -	
				SCALE 1:2		SHEET 2 OF 4	
						REV B	

P	LTR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET 1	-	-	-



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN DAVID LI 02JUL2015	 TE Connectivity			
DIMENSIONS:		CHK CHRIS WANG 02JUL2015				
mm	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD XU XIANG 02JUL2015	NAME H24B-SGR/SDR/SDRM/SGRH/SDRH/ SDRHM-LB-PG/M			
	0 PLC ±	PRODUCT SPEC	SIZE A2			
	1 PLC ±	APPLICATION SPEC	CAGE CODE -			
	2 PLC ±	108-137013	DRAWING NO C-T16X0243XXXX00			
	3 PLC ±	114-137013	RESTRICTED TO -			
	4 PLC ±	WEIGHT -	SCALE 1:2			
MATERIAL	FINISH	Customer Drawing	SHEET 3 OF 4			
-	-		REV B			
-	-					

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

20

© COPYRIGHT 20

BY -

ALL RIGHTS RESERVED.

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
-		SEE SHEET 1	-	-	-

T1650243121-000	H24B-SGRH-LB-PG21	H24B HOUSING,SURFACE MOUNTED,METAL SINGLE LOCKING,PG21,HIGH CONSTRUCTION,POWDER COATED,GREY H24B下壳,表面安装,彩锌单扣,PG21,高结构,灰色粉末喷涂	PG21	-	TYPE 5 类 型 5
T1650243125-000	H24B-SGRH-LB-M25	H24B HOUSING,SURFACE MOUNTED,METAL SINGLE LOCKING,M25,HIGH CONSTRUCTION,POWDER COATED,GREY H24B下壳,表面安装,彩锌单扣,M25,高结构,灰色粉末喷涂	M25	-	
T1650243129-000	H24B-SGRH-LB-PG29	H24B HOUSING,SURFACE MOUNTED,METAL SINGLE LOCKING,PG29,HIGH CONSTRUCTION,POWDER COATED,GREY H24B下壳,表面安装,彩锌单扣,PG29,高结构,灰色粉末喷涂	PG29	-	
T1650243132-000	H24B-SGRH-LB-M32	H24B HOUSING,SURFACE MOUNTED,METAL SINGLE LOCKING,M32,HIGH CONSTRUCTION,POWDER COATED,GREY H24B下壳,表面安装,彩锌单扣,M32,高结构,灰色粉末喷涂	M32	-	
T1650243221-000	H24B-SGRH-LB-2PG21	H24B HOUSING,SURFACE MOUNTED,METAL SINGLE LOCKING,2PG21,HIGH CONSTRUCTION,POWDER COATED,GREY H24B下壳,表面安装,彩锌单扣,2PG21,高结构,灰色粉末喷涂	PG21	PG21	
T1650243229-000	H24B-SGRH-LB-2PG29	H24B HOUSING,SURFACE MOUNTED,METAL SINGLE LOCKING,2PG29,HIGH CONSTRUCTION,POWDER COATED,GREY H24B下壳,表面安装,彩锌单扣,2PG29,高结构,灰色粉末喷涂	PG29	PG29	
T1650243232-000	H24B-SGRH-LB-2M32	H24B HOUSING,SURFACE MOUNTED,METAL SINGLE LOCKING,2M32,HIGH CONSTRUCTION,POWDER COATED,GREY H24B下壳,表面安装,彩锌单扣,2M32,高结构,灰色粉末喷涂	M32	M32	TYPE 6 类 型 6
T1660243121-000	H24B-SDRH-LB-PG21	H24B HOUSING,SURFACE MOUNTED,METAL SINGLE LOCKING,PG21,HIGH CONSTRUCTION,PLASTIC PROTECTION COVER,POWDER COATED,GREY H24B下壳,表面安装,彩锌单扣,PG21,高结构,带塑料保护盖,灰色粉末喷涂	PG21	-	
T1660243129-000	H24B-SDRH-LB-PG29	H24B HOUSING,SURFACE MOUNTED,METAL SINGLE LOCKING,PG29,HIGH CONSTRUCTION,PLASTIC PROTECTION COVER,POWDER COATED,GREY H24B下壳,表面安装,彩锌单扣,PG29,高结构,带塑料保护盖,灰色粉末喷涂	PG29	-	
T1660243132-000	H24B-SDRH-LB-M32	H24B HOUSING,SURFACE MOUNTED,METAL SINGLE LOCKING,M32,HIGH CONSTRUCTION,PLASTIC PROTECTION COVER,POWDER COATED,GREY H24B下壳,表面安装,彩锌单扣,M32,高结构,带塑料保护盖,灰色粉末喷涂	M32	-	
T1660243221-000	H24B-SDRH-LB-2PG21	H24B HOUSING,SURFACE MOUNTED,METAL SINGLE LOCKING,2PG21,HIGH CONSTRUCTION,PLASTIC PROTECTION COVER,POWDER COATED,GREY H24B下壳,表面安装,彩锌单扣,2PG21,高结构,带塑料保护盖,灰色粉末喷涂	PG21	PG21	
T1660243229-000	H24B-SDRH-LB-2PG29	H24B HOUSING,SURFACE MOUNTED,METAL SINGLE LOCKING,2PG29,HIGH CONSTRUCTION,PLASTIC PROTECTION COVER,POWDER COATED,GREY H24B下壳,表面安装,彩锌单扣,2PG29,高结构,带塑料保护盖,灰色粉末喷涂	PG29	PG29	
T1660243232-000	H24B-SDRH-LB-2M32	H24B HOUSING,SURFACE MOUNTED,METAL SINGLE LOCKING,2M32,HIGH CONSTRUCTION,PLASTIC PROTECTION COVER,POWDER COATED,GREY H24B下壳,表面安装,彩锌单扣,2M32,高结构,带塑料保护盖,灰色粉末喷涂	M32	M32	TYPE 7 类 型 7
T1660243121-100	H24B-SDRHM-LB-PG21	H24B HOUSING,SURFACE MOUNTED,METAL SINGLE LOCKING,PG21,HIGH CONSTRUCTION,METAL PROTECTION COVER,POWDER COATED,GREY H24B下壳,表面安装,彩锌单扣,PG21,高结构,带金属保护盖,灰色粉末喷涂	PG21	-	
T1660243129-100	H24B-SDRHM-LB-PG29	H24B HOUSING,SURFACE MOUNTED,METAL SINGLE LOCKING,PG29,HIGH CONSTRUCTION,METAL PROTECTION COVER,POWDER COATED,GREY H24B下壳,表面安装,彩锌单扣,PG29,高结构,带金属保护盖,灰色粉末喷涂	PG29	-	
T1660243132-100	H24B-SDRHM-LB-M32	H24B HOUSING,SURFACE MOUNTED,METAL SINGLE LOCKING,M32,HIGH CONSTRUCTION,METAL PROTECTION COVER,POWDER COATED,GREY H24B下壳,表面安装,彩锌单扣,M32,高结构,带金属保护盖,灰色粉末喷涂	M32	-	
T1660243221-100	H24B-SDRHM-LB-2PG21	H24B HOUSING,SURFACE MOUNTED,METAL SINGLE LOCKING,2PG21,HIGH CONSTRUCTION,METAL PROTECTION COVER,POWDER COATED,GREY H24B下壳,表面安装,彩锌单扣,2PG21,高结构,带金属保护盖,灰色粉末喷涂	PG21	PG21	
T1660243229-100	H24B-SDRHM-LB-2PG29	H24B HOUSING,SURFACE MOUNTED,METAL SINGLE LOCKING,2PG29,HIGH CONSTRUCTION,METAL PROTECTION COVER,POWDER COATED,GREY H24B下壳,表面安装,彩锌单扣,2PG29,高结构,带金属保护盖,灰色粉末喷涂	PG29	PG29	
T1660243232-100	H24B-SDRHM-LB-2M32	H24B HOUSING,SURFACE MOUNTED,METAL SINGLE LOCKING,2M32,HIGH CONSTRUCTION,METAL PROTECTION COVER,POWDER COATED,GREY H24B下壳,表面安装,彩锌单扣,2M32,高结构,带金属保护盖,灰色粉末喷涂	M32	M32	
PART NUMBER 料 号	DESCRIPTION 描 述		IG1	IG2	TYPE 类 型

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm

MATERIAL
-
-

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ±
1 PLC ±
2 PLC ±
3 PLC ±
4 PLC ±
ANGLES ±
FINISH -
-

DWN
DAVID LI
CHK
CHRIS WANG
APVD
XU XIANG
PRODUCT SPEC
108-137013
APPLICATION SPEC
114-137013
WEIGHT
-

Customer Drawing

02JUL2015
02JUL2015
02JUL2015

NAME
H24B-SGR/SDR/SDRM/SGRH/SDRH/
SDRHM-LB-PG/M

SIZE
A2

CAGE CODE
-

DRAWING NO
T16X0243XXXX00

RESTRICTED TO
-

SCALE
1:2

SHEET
4

OF
4

REV
B

TE Connectivity

TE

1471-9 (3/13)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[T1650243221-000](#)