




TYPE I

类型 I



TYPE 2

类型 2



All dimension is same as TYPE I, except those defined in this TYPE
除了在本类型中定义的尺寸外, 其他尺寸同类型 I

NOTES:
1. TECHNICAL CHARACTERISTICS:
HOOD MATERIAL: DIE CAST ALUMINIUM ALLOY
SURFACE: SEE TABLE
DEGREE OF PROTECTION: IP68 (MATED)

注释
1. 技术参数:
壳体材料: 铝合金
表面处理: 见表格
防护等级: IP68 (配合)

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	INITIAL RELEASE	08OCT2016	DW	CW
	A1	ECR-17-018159	13DEC2017	RL	CW
	B	ECR-19-009256	23FEB2019	CD	CW
	C	ECR-20-016312	04JUN2021	BS	CW

THIS DRAWING IS A CONTROLLED DOCUMENT.			DWN 08OCT2016 DAVID WANG CHK 08OCT2016 CHRIS WANG APVD 08OCT2016 XIANG XU			TE Connectivity		
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:		PRODUCT SPEC 108-137191		NAME H16BPR-TGHC-PG/M-EMC-C		
MATERIAL -		FINISH -		APPLICATION SPEC 114-137191		SIZE A2	CAGE CODE -	DRAWING NO T192216XXXXX09
Customer Drawing			SCALE 1:1		SHEET 1 OF 2		REV C	

printed on 8 Jun 2021 09:25 (China Standard Time) from IE236667

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

20

© COPYRIGHT 20

BY -

ALL RIGHTS RESERVED.

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET 1	-	-	-

NOTES:

SEE SHEET 1


备注:

见 SHEET 1

T1922160225-009	H16BPR-TGHC-2M25-EMC-C	H16BPR HOOD,CENTER LOCKING,TOP ENTRY 2M25,BLACK H16BPR上壳,中部锁定,顶出2M25,黑色	M25	M25	-	TYPE 2 类型2
T1922162150-009	H16BPR-TGHC-M50-EMC-C	H16BPR HOOD,CENTER LOCKING,TOP ENTRY M50,GREY H16BPR上壳,中部锁定,顶出M50,灰色	-	-	M50	TYPE 1 类型1
T1922161140-009	H16BPR-TGHC-M40-EMC-C	H16BPR HOOD,CENTER LOCKING,TOP ENTRY M40,SILVER WHITE H16BPR上壳,中部锁定,顶出M40,银白色	-	-	M40	
T1922161136-009	H16BPR-TGHC-PG36-EMC-C	H16BPR HOOD,CENTER LOCKING,TOP ENTRY PG36,SILVER WHITE H16BPR上壳,中部锁定,顶出PG36,银白色	-	-	PG36	
T1922161132-009	H16BPR-TGHC-M32-EMC-C	H16BPR HOOD,CENTER LOCKING,TOP ENTRY M32,SILVER WHITE H16BPR上壳,中部锁定,顶出M32,银白色	-	-	M32	
T1922161129-009	H16BPR-TGHC-PG29-EMC-C	H16BPR HOOD,CENTER LOCKING,TOP ENTRY PG29,SILVER WHITE H16BPR上壳,中部锁定,顶出PG29,银白色	-	-	PG29	
T1922161125-009	H16BPR-TGHC-M25-EMC-C	H16BPR HOOD,CENTER LOCKING,TOP ENTRY M25,SILVER WHITE H16BPR上壳,中部锁定,顶出M25,银白色	-	-	M25	
T1922161121-009	H16BPR-TGHC-PG21-EMC-C	H16BPR HOOD,CENTER LOCKING,TOP ENTRY PG21,SILVER WHITE H16BPR上壳,中部锁定,顶出PG21,银白色	-	-	PG21	
T1922160140-009	H16BPR-TGHC-M40-EMC-C	H16BPR HOOD,CENTER LOCKING,TOP ENTRY M40,BLACK H16BPR上壳,中部锁定,顶出M40,黑色	-	-	M40	
T1922160136-009	H16BPR-TGHC-PG36-EMC-C	H16BPR HOOD,CENTER LOCKING,TOP ENTRY PG36,BLACK H16BPR上壳,中部锁定,顶出PG36,黑色	-	-	PG36	
T1922160132-009	H16BPR-TGHC-M32-EMC-C	H16BPR HOOD,CENTER LOCKING,TOP ENTRY M32,BLACK H16BPR上壳,中部锁定,顶出M32,黑色	-	-	M32	
T1922160129-009	H16BPR-TGHC-PG29-EMC-C	H16BPR HOOD,CENTER LOCKING,TOP ENTRY PG29,BLACK H16BPR上壳,中部锁定,顶出PG29,黑色	-	-	PG29	
T1922160125-009	H16BPR-TGHC-M25-EMC-C	H16BPR HOOD,CENTER LOCKING,TOP ENTRY M25,BLACK H16BPR上壳,中部锁定,顶出M25,黑色	-	-	M25	
T1922160121-009	H16BPR-TGHC-PG21-EMC-C	H16BPR HOOD,CENTER LOCKING,TOP ENTRY PG21,BLACK H16BPR上壳,中部锁定,顶出PG21,黑色	-	-	PG21	
PART NUMBER 料号	DESCRIPTION 描述		PG/M THREAD-3 PG/M 螺纹-3	PG/M THREAD-2 PG/M 螺纹-2	PG/M THREAD-1 PG/M 螺纹-1	TYPE 类型

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm



MATERIAL
-

-

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ±-

1 PLC ±-

2 PLC ±-

3 PLC ±-

4 PLC ±-

ANGLES ±-

FINISH

-

-

DWN
DAVID WANG
08OCT2016

CHK
CHRIS WANG
08OCT2016


APVD
XIANG XU
08OCT2016

PRODUCT SPEC
108-137191

APPLICATION SPEC
114-137191

WEIGHT
-

Customer Drawing

TE Connectivity

NAME
H16BPR-TGHC-PG/M-EMC-C

SIZE
A2

CAGE CODE
-

DRAWING NO
T192216XXXXX09

RESTRICTED TO
-

SCALE
1:1

SHEET
2

OF
2

REV
C

printed on 8 Jun 2021 09:25 (China Standard Time) from IE236667

1471-9 (3/13)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[H16BPR-TGHC-M32-EMC-C](#)