

TYPE 1

Housing with TE Logo

2XM6 NUT

4XM3 THREAD

4XØ6.5

58

39

32

27

57

81

83

126.2

146

29

20

TE

IP68

CE

TE

IP68

CE

TYPE 2

Housing without Logo

*Without Logo

IP68

CE

IP68

CE

NOTES:

1. TECHNICAL CHARACTERISTICS:

HOUSING MATERIAL: DIE CAST ALUMINIUM ALLOY

SURFACE TREATMENT: SEE TABLE

DEGREE OF PROTECTION: IP68 (MATED)

注释

1. 技术参数:

壳体材料: 铝合金

表面处理: 见表格

防护等级: IP68 (配合)

Panel Cut Out

83

60

35

32

T1930100000-100	POWDER COATED BLACK	H10BPR-AG	TYPE 2
T1930102000-000	POWDER COATED GRAY	H10BPR-AG	TYPE1
T1930101000-000	POWDER COATED SILVER WHITE	H10BPR-AG	
T1930100000-000	POWDER COATED BLACK	H10BPR-AG	
PART NUMBER	SURFACE TREATMEN	DESCRIPTION	TYPE

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:
0 PLC ±:
1 PLC ±:
2 PLC ±:
3 PLC ±:
4 PLC ±:
ANGLES ±:
FINISH -
-

DWN 10JUN2015
Gino.Yao

CHK 10JUN2015
Chris.Wang

APVD 10JUN2015
Xiang.Xu

PRODUCT SPEC
108-137014

APPLICATION SPEC
114-137014

WEIGHT -

Customer Drawing

TE

TE Connectivity

NAME
H10BPR-AG

SIZE
A2

CAGE CODE
-

DRAWING NO
T193010XXXXX00

RESTRICTED TO
-

SCALE
1:1

SHEET
1

OF
1

REV
B

1471-9 (3/13)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[T1930100000-100](#)