

printed on 18 Jun 2021 14:59 (China Standard Time) from TE236667

D

A

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

20






© COPYRIGHT 20

BY -

ALL RIGHTS RESERVED.



REVISIONS

| P | LTR | DESCRIPTION | DATE | DWN | APVD |
|---|-----|---------------|-----------|-----|------|
| | A | INITIAL | 18DEC2014 | DW | CW |
| | B | ECR-15-013750 | 21SEP2015 | DW | CW |
| | B1 | ECR-15-016224 | 05NOV2015 | DW | CW |
| | C | ECR-20-016101 | 09JUN2021 | BS | CW |



NOTES:
1. TECHNICAL CHARACTERISTICS:
INSULATION MATERIAL: PC
RATED VOLTAGE: 400 V
RATED CURRENT: 10 A
INSULATION RESISTANCE: $\geq 400\text{M}\Omega$
RATED IMPULSE VOLTAGE: 4 KV
POLLUTION DEGREE: 3
FLAMMABILITY: UL94V-0
MATING CYCLES: 500 CYCLES
WIRE RANGE: 0.5-2.5 mm² (20-14 AWG)
CONTACT FINISH: SILVER PLATED
CONTACT TYPE: SPRING CONTACT

注释:
1. 技术参数:
绝缘材料: PC
额定电压: 400V
额定电流: 10A
绝缘电阻: $\geq 400\text{M}\Omega$
额定脉冲电压: 4 KV
污染等级: 3
阻燃等级: UL94V-0
插拔次数: 500 次
接线范围: 0.5-2.5 mm² (20-14 AWG)
端子表面处理: 镀银
接线类型: 弹片压接

| | | | | | | | | | | | |
|---|--|--|--------------------------------|--|---|--------------|--|--------------------|--|--------------------------------|--|
| THIS DRAWING IS A CONTROLLED DOCUMENT. | | | DWN DAVID WANG 18DEC2014 | |  TE Connectivity | | | | | | |
| DIMENSIONS: mm | | | CHK CHRIS WANG 18DEC2014 | | NAME HA-004-MS | | | | | | |
| | | | APVD XU XIANG 18DEC2014 | | | | | | | | |
|  | | | PRODUCT SPEC 108-137045 | | SIZE A3 | | | | | | |
| | | | APPLICATION SPEC 114-137045 | | | | | | | | |
| | | | MATERIAL - | | | WEIGHT - | | CAGE CODE 00779 | | DRAWING NO C-T2010043101000 | |
| FINISH - | | | Customer Drawing | | | SCALE 2:1 | | SHEET 1 OF 1 | | REV C | |

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[T2010043101-000](#)