









PANEL CUT OUT DIMENSION FOR INSERT
WITHOUT HOODS/HOUSING, ONLY FOR REFERENCE
不使用防护外壳时芯件的开孔安装尺寸, 仅供参考



4X M3 SCREW, RECOMMENDED
TIGHTENING TORQUE 0.5Nm
4X M3 螺丝, 推荐扭力矩为 0.5Nm

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APV
	A	INITIAL	24NOV2016	DW	CW
	B	ECR-21-106515	21JUL2021	SQ	CW


NOTES:

- I. TECHNICAL CHARACTERISTICS:
INSULATION MATERIAL: PC
RATED VOLTAGE: 500V
RATED CURRENT: 16A
INSULATION RESISTANCE: $\geq 400\text{M}\Omega$
RATED IMPULSE VOLTAGE: 6KV
POLLUTION DEGREE: 3
FLAMMABILITY: UL94V-0
MATING CYCLES: 500 CYCLES
WIRE RANGE: $0.5\text{mm}^2 \sim 2.5\text{mm}^2$ (AWG20-AWG14)
CONTACT FINISH: SILVER PLATED
CONTACT TYPE: DOUBLE SPRING CLAMP

注释：

- 技术参数：
绝缘材料：PC
额定电压：500V
额定电流：16A
绝缘电阻： $\geq 400M\Omega$
脉冲电压：6KV
污染等级：3
阻燃等级：UL94V-0
插拔次数：500次
接线范围： $0.5mm^2 \sim 2.5mm^2$ （AWG20-AWG14）
端子表面处理：镀银
接线类型：双弹片连接

T2040105201-000	HE-010-FSS	HE-010 FEMALE INSERT, DOUBLE SPRING CLAMP HE-010母插, 双弹片
PART NUMBER 料号	PART DESCRIPTION 描述	

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 24NOV2016 DAVID WANG		 TE Connectivity													
		CHK 24NOV2016 CHRIS WANG															
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ±- 1 PLC ±- 2 PLC ±- 3 PLC ±- 4 PLC ±- ANGLES ±- ±-		APVD 24NOV2016 XIANG XU				NAME HE-010-FSS									
				PRODUCT SPEC 108-137044		SIZE A3				CAGE CODE 00779		DRAWING NO C-T2040105201000		RESTRICTED TO 1			
				APPLICATION SPEC 114-137044													
				WEIGHT -													
MATERIAL - -		FINISH - -		CUSTOMER DRAWING								SCALE 1:1		SHEET 1 OF 1		REV B	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[T2040105201-000](#)