







DETAIL A
4:1




TYPE-1, T2050102201-000, TE LOGO
类型-1, T2050102201-000, TE LOGO

- NOTES:
- TECHNICAL CHARACTERISTICS:
INSULATION MATERIAL: PC
RATED VOLTAGE: 500 V
RATED CURRENT: 16 A
INSULATION RESISTANCE: $\geq 400M\Omega$
RATED IMPULSE VOLTAGE: 6 KV
POLLUTION DEGREE: 3
FLAMMABILITY: UL94V-0
MATING CYCLES: 500 CYCLES
WIRE RANGE: 0.14-4 mm² (26-12 AWG)
CONTACT TYPE: CRIMP CONTACT
 - CONTACT NEED TO BE ORDERED SEPARATELY.
(ORDER No. T20300X20XX-000)






M4 SCREW, RECOMMENDED
TIGHTENING TORQUE 1.2Nm
M4螺丝, 推荐锁紧力矩1.2Nm




4X M3 SCREW, RECOMMENDED
TIGHTENING TORQUE 0.5Nm
4X M3螺丝, 推荐锁紧力矩0.5Nm

DETAIL A




PANEL CUT FOR INSERTS FOR USING
WITHOUT HOODS/ HOUSINGS
不使用防护外壳时芯件的安装开孔图






- 注释:
- 技术参数:
绝缘材料: PC
额定电压: 500V
额定电流: 16A
绝缘电阻: $\geq 400M\Omega$
额定脉冲电压: 6 KV
污染等级: 3
阻燃等级: UL94V-0
插拔次数: 500次
接线范围: 0.14-4 mm² (26-12 AWG)
接线类型: 冷压接
 - 端子需要单独订购.
(订货号 T20300X20XX-000)

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN DAVID LI 09MAR2015		TE Connectivity									
DIMENSIONS: mm		CHK CHRIS WANG 09MAR2015											
		APVD XU XIANG 09MAR2015											
		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME HEE-010-F									
		0 PLC ±-											
		1 PLC ±-											
		2 PLC ±-											
3 PLC ±-													
4 PLC ±-													
ANGLES ±-		PRODUCT SPEC 108-106137		SIZE A3									
MATERIAL -		APPLICATION SPEC 114-106137						CAGE CODE -		DRAWING NO C-T2050102201000		RESTRICTED TO -	
FINISH -		WEIGHT -						SCALE 1:1		SHEET 1 OF 3		REV C	
-				Customer Drawing									

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET 1	-	-	-



DETAIL B
4:1




NOTE:
SEE SHEET 1


注释:
见页 1

DETAIL B


TYPE-2,T2059102201-000,NO TE LOGO
类型-2,T2059102201-000,无TE LOGO



ALL SPEC DIMENSION REFER TO TYPE 1
所有产品规格尺寸参照 TYPE 1






THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN DAVID LI 09MAR2015		 TE Connectivity						
		CHK CHRIS WANG 09MAR2015								
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ±° 1 PLC ±° 2 PLC ±° 3 PLC ±° 4 PLC ±° ANGLES ±°		APVD XU XIANG 09MAR2015		NAME HEE-010-F				
				PRODUCT SPEC 108-106137						
				APPLICATION SPEC 114-106137						
				SIZE				CAGE CODE	DRAWING NO	RESTRICTED TO
				MATERIAL				FINISH		
-		-		A3		-	©-T2050102201000	-		
-		-		Customer Drawing				SCALE 1:1	SHEET 2 OF 3	REV C

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET 1	-	-	-



NOTE:
SEE SHEET 1

注释:
见页 1



TYPE-3,T2050102201-001,STAINLESS STEEL SCREW,NO LOGO
类型-3,T2050102201-001,不锈钢螺丝,无LOGO

ALL SPEC DIMENSION REFER TO TYPE 1
所有产品规格尺寸参照 TYPE 1

T2050102201-001	HEE-010-F	HEE-010 FEMALE INSERT, STAINLESS STEEL SCREW,NO LOGO HEE-010 母插,不锈钢螺丝,无LOGO	TYPE-3 类型-3
T2059102201-000	HEE-010-F	HEE-010 FEMALE INSERT,NO TE LOGO HEE-010 母插,无TE LOGO	TYPE-2 类型-2
T2050102201-000	HEE-010-F	HEE-010 FEMALE INSERT HEE-010 母插	TYPE-1 类型-1
PART NUMBER 料 号	PART DESCRIPTION 描 述		TYPE 类 型

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN DAVID LI 09MAR2015	TE Connectivity NAME HEE-010-F		
		CHK CHRIS WANG 09MAR2015			
		APVD XU XIANG 09MAR2015			
		PRODUCT SPEC 108-106137			
DIMENSIONS: mm	TOLERANCES UNLESS OTHERWISE SPECIFIED:		APPLICATION SPEC 114-106137		SIZE A3
	0 PLC	±-	WEIGHT		CAGE CODE
	1 PLC	±-			DRAWING NO
	2 PLC	±-			RESTRICTED TO
	3 PLC	±-			
	4 PLC	±-			
	ANGLES	±-			
MATERIAL	FINISH				
-	-				
-	-				
Customer Drawing			SCALE 1:1	SHEET 3 OF 3	REV C

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[T2059102201-000](#)