





REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	INITIAL	05MAR2015	DW	CW
	B	ECR-15-015267	20OCT2015	DW	CW
	BI	ECR-16-017313	07DEC2016	DW	CW
	C	ECR-21-111798	03SEP2021	WQR	CW



- NOTES:
1. TECHNICAL CHARACTERISTICS:
INSULATION MATERIAL: PC
RATED VOLTAGE: 500V
RATED CURRENT: 16A
INSULATION RESISTANCE: $\geq 400M\Omega$
RATED IMPULSE VOLTAGE: 6KV
POLLUTION DEGREE: 3
FLAMMABILITY: UL94V-0
MATING CYCLES: 500 CYCLES
WIRE RANGE: $0.14mm^2 \sim 4mm^2$ (AWG26-AWG12)
CONTACT TYPE: CRIMP CONTACT
 2. CONTACTS NEED TO BE ORDERED SEPARATELY.
(ORDER No. REFER TO DRAWING: T20300X20XX000)

- 注释:
1. 技术参数:
绝缘材料: PC
额定电压: 500V
额定电流: 16A
绝缘电阻: $\geq 400M\Omega$
脉冲电压: 6KV
污染等级: 3
阻燃等级: UL94V-0
插拔次数: 500次
接线范围: $0.14mm^2 \sim 4mm^2$ (AWG26-AWG12)
接线类型: 冷压接
 2. 端子需要单独订购.
(订货号参考图面: T20300X20XX000)




PANEL CUT OUT DIMENSION FOR INSERT
WITHOUT HOOD/HOUSING, ONLY FOR REFERENCE
不使用防护外壳时芯件的开孔安装尺寸, 仅供参考

M4 SCREW, RECOMMENDED
TIGHTENING TORQUE 1.2Nm
M4螺丝, 推荐扭力矩为1.2Nm



T2050643201-000	HEEE-064-F	HEEE-064 FEMALE INSERT HEEE-064 母插			
PART NUMBER 料 号		PART DESCRIPTION 描 述			

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN David Wang 05MAR2015	 TE Connectivity						
DIMENSIONS: mm		CHK Chris Wang 05MAR2015	NAME HEEE-064-F						
		APVD Xiang Xu 05MAR2015							
0 PLC ±- 1 PLC ±- 2 PLC ±- 3 PLC ±- 4 PLC ±- ANGLES ±-		PRODUCT SPEC 108-137068	SIZE A3			CAGE CODE 00779	DRAWING NO C-T2050643201000	RESTRICTED TO -	
		APPLICATION SPEC 114-137068							
		MATERIAL - -	FINISH - -	WEIGHT -					
Customer Drawing						SCALE 1:1	SHEET 1	OF 1	REV C

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[T2050643201-000](#)