







REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	INITIAL	29APR2015	DW	CW
	B	ECR-15-018270	09DEC2015	DW	CW
	C	ECR-21-111798	27SEP2021	WQR	CW



NOTES:
1. TECHNICAL CHARACTERISTICS:
INSULATION MATERIAL: PC
RATED VOLTAGE: 400V
RATED CURRENT: 16A
INSULATION RESISTANCE: $\geq 400M\Omega$
RATED IMPULSE VOLTAGE: 6KV
POLLUTION DEGREE: 3
CONTACT RESISTANCE: $\leq 5m\Omega$
FLAMMABILITY: UL94V-0
MATING CYCLES: 500 CYCLES
OPERATION TEMPERATURE: $-40^{\circ}C \sim +125^{\circ}C$
WIRE RANGE: 0.5~2.5mm²
CONTACT TYPE: SPRING TYPE.

注释:
1. 技术参数:
绝缘材料: PC
额定电压: 400V
额定电流: 16A
绝缘电阻: $\geq 400M\Omega$
脉冲电压: 6KV
污染等级: 3
接触电阻: $\leq 5m\Omega$
阻燃等级: UL94V-0
插拔次数: 500次
工作温度: $-40^{\circ}C \sim +125^{\circ}C$
接线范围: 0.5~2.5mm²
接线类型: 弹片连接

HMN-005-FS	T2110052201-000
DESCRIPTION	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN	29APR2015	TE Connectivity		
		CHK	29APR2015			
		APVD	29APR2015			
		PRODUCT SPEC	108-137119			
		APPLICATION SPEC	114-137119	NAME HMN-005-FS		
		WEIGHT	-			
		Customer Drawing			SCALE	3:2
					SHEET	1 OF 1
					REV	C

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[T2110052201-000](#)