






REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	INITIAL	18MAR2015	DW	CW
	B	ECR-15-018270	07DEC2015	DW	CW
	BI	ECR-18-000057	03JAN2018	YC	CW
	C	ECR-21-111798	22SEP2021	WQR	CW

NOTES:


1. TECHNICAL CHARACTERISTICS:
INSULATION MATERIAL: PC
RATED VOLTAGE: 1000V
RATED CURRENT: 200A
INSULATION RESISTANCE: $\geq 400M\Omega$
RATED IMPULSE VOLTAGE: 8KV
POLLUTION DEGREE: 3
CONTACT RESISTANCE: $\leq 0.5m\Omega$
FLAMMABILITY: UL94V-0
MATING CYCLES: 500 CYCLES
WIRE RANGE: 25mm²~70mm²
CONTACT TYPE: CRIMP TYPE.

注释:

1. 技术参数:
绝缘材料: PC
额定电压: 1000V
额定电流: 200A
绝缘电阻: $\geq 400M\Omega$
脉冲电压: 8KV
污染等级: 3
接触电阻: $\leq 0.5m\Omega$
阻燃等级: UL94V-0
插拔次数: 500次
接线范围: 20mm²~70mm²
接线类型: 压接



T2111013201-000 AS SHOWN,
WITH TE LOGO AND UL MARK.
T2111013201-000 如图所示,
带 TE LOGO 和 UL 认证标志.



T2111013201-001 AS SHOWN,ALL DIMENSIONS ARE
SAME AS T2111013201-000,EXCEPT NO TE
LOGO,NO UL MARK.
T2111013201-001 如图所示,除了不带 TE LOGO 和 UL
认证标志外,其余所有尺寸同料号 T2111013201-000 一致.

T2111013201-001	HMN-001-FC	HMN-001 FEMALE MODULE INSERT,CRIMP,NO LOGO HMN-001 冷压模块母插,无LOGO
T2111013201-000	HMN-001-FC	HMN-001 FEMALE MODULE INSERT,CRIMP HMN-001 冷压模块母插
PART NUMBER 料 号	PART DESCRIPTION 描 述	

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 18MAR2015 DAVID WANG	 TE Connectivity		
DIMENSIONS: mm		CHK 18MAR2015 CHRIS WANG			
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD 18MAR2015 XIANG XU	NAME HMN-001-FC		
0 PLC ± 1 PLC ± 2 PLC ± 3 PLC ± 4 PLC ± ANGLES ±		PRODUCT SPEC 108-137057	SIZE A3		
MATERIAL -		APPLICATION SPEC 114-137057	CAGE CODE 00779		
FINISH -		WEIGHT -	DRAWING NO T2111013201000		
CUSTOMER DRAWING		SCALE 1:1		SHEET 1 OF 1	REV C

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[T2111013201-000](#)