


REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	INITIAL	22APR2015	DW	CW
	B	ECR-15-018270	09DEC2015	DW	CW
	B1	ECR-16-006849	13MAY2016	RL	CW
	C	ECR-21-122216	03DEC2021	WOR	CW



注释:

1. 技术参数:

绝缘材料:	PC
额定电压:	50V
额定电流:	见表格
绝缘电阻:	$> 400\text{M}\Omega$
额定脉冲电压:	0.8KV
污染等级:	见表格
阻燃等级:	UL94V-0
插拔次数:	500次
工作温度:	$-40 \sim +125^{\circ}\text{C}$
接线范围:	见表格
接线类型:	冷压接

2. 端子需要单独订购。

T2111027101-003	HMN-Q-M WITHOUT LOGO HMN-Q 模块公插 不带LOGO	-	-	-	WITHOUT LOGO, TUV, UL OR CUL MARK 不带LOGO, TUV, UL和CUL激光打标
T2111027101-002	HMN-Q3-M HMN-Q3模块公插5A	5A	2	0.08~0.52 mm ² (28~20 AWG)	WITH LOGO, TUV AND UL MARK 带LOGO, TUV和UL激光打标
T2111027101-001	HMN-Q2-M HMN-Q2模块公插10A	10A	3	0.14~2.5 mm ² (26~14 AWG)	WITH LOGO, TUV AND CUL MARK 带LOGO, TUV和CUL激光打标
T2111027101-000	HMN-Q1-M HMN-Q1模块公插16A	16A	3	0.14~4 mm ² (26~12 AWG)	WITH LOGO, TUV AND CUL MARK 带LOGO, TUV和CUL激光打标
PART NUMBER 料 号	"X" TYPE "X" 产品型号	"XX"A "XX"电流	"X" PD "X"污染等级	WIRE GAUGE 线 规	REMARK 备 注

1471-9 (3/13)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[T2111027101-002](#)