

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	INITIAL	18MAR2015	DW	CW
	B	ECR-15-018270	07DEC2015	DW	CW
	C	ECR-21-111798	23SEP2021	WQR	CW

NOTES:

1. TECHNICAL CHARACTERISTICS:
INSULATION MATERIAL: PC
RATED VOLTAGE: 1000V
RATED CURRENT: 100A
INSULATION RESISTANCE: >=400MΩ
RATED IMPULSE VOLTAGE: 8KV
POLLUTION DEGREE: 3
FLAMMABILITY: UL94V-0
MATING CYCLES: 500 CYCLES
OPERATION TEMPERATURE: -40°C~+125°C
WIRE RANGE: 10.0mm²~35.0mm²
CONTACT TYPE: CRIMP CONTACT


2. CONTACT NEED TO BE ORDERED SEPARATELY.
(ORDER No. REFER TO DRAWING:T20500010XX000)

注释:

1. 技术参数:
绝缘材料: PC
额定电压: 1000V
额定电流: 100A
绝缘电阻: >=400MΩ
脉冲电压: 8KV
污染等级: 3
阻燃等级: UL94V-0
插拔次数: 500次
工作温度: -40°C~+125°C
接线范围: 10.0mm²~35.0mm²
接线类型: 冷压接

2. 端子需要单独订购.
(订货号参考图面: T20500010XX000)

HMN-D2-MC	T2111028101-000
DESCRIPTION	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.			DWN David Wang 18MAR2015		TE Connectivity								
			CHK Chris. Wang 18MAR2015										
			APVD Xiang Xu 18MAR2015										
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME HMN-D2-MC									
		0 PLC ±-											
		1 PLC ±-											
		2 PLC ±-											
		3 PLC ±-											
4 PLC ±-		PRODUCT SPEC		108-137058									
ANGLES ±-		APPLICATION SPEC											
		114-137058											
MATERIAL		FINISH		WEIGHT		SIZE		CAGE CODE		DRAWING NO		RESTRICTED TO	
-		-		-		A3		00779		C-T2111028101000		-	
-		-		Customer Drawing		SCALE		1:1		SHEET		1 OF 1	
												REV C	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[T2111028101-000](#)