








REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	INITIAL	04JUL2018	YC	CW
	B	ECR-21-111798	27SEP2021	WQR	CW



- NOTES:
- TECHNICAL CHARACTERISTICS:
INSULATION MATERIAL: PC
RATED VOLTAGE: 400V
RATED CURRENT: 16A
INSULATION RESISTANCE: $\geq 400M\Omega$
RATED IMPULSE VOLTAGE: 6KV
POLLUTION DEGREE: 3
FLAMMABILITY: UL94V-0
MATING CYCLES: 500 CYCLES
WIRE RANGE: 0.14~4 mm² (26~12 AWG)
CONTACT TYPE: CRIMP CONTACT
 - CONTACT NEED TO BE ORDERED SEPARATELY.
(ORDER No. REFER TO DRAWING:T20300X10XX000)

- 注释:
- 技术参数:
绝缘材料: PC
额定电压: 400V
额定电流: 16A
绝缘电阻: $\geq 400M\Omega$
额定脉冲电压: 6KV
污染等级: 3
阻燃等级: UL94V-0
插拔次数: 500次
接线范围: 0.14~4 mm² (26~12 AWG)
接线类型: 冷压接
 - 端子需要单独订购.
(订货号参考图面: T20300X10XX000)

T2111082101-100	HMN-008-M 9-16	HMN-008 MALE MODULE INSERT 9-16 HMN-008 模块公插, 9-16			
PART NUMBER 成品料号		PART DESCRIPTION 产品描述			

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN YORK CHEN 04JUL2018	 TE Connectivity				
DIMENSIONS: mm		CHK GINO YAO 04JUL2018	NAME HMN-008-M 9-16				
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD CHRIS WANG 04JUL2018					
		PRODUCT SPEC 108-137061	RESTRICTED TO				
0 PLC ± 1 PLC ± 2 PLC ± 3 PLC ± 4 PLC ± ANGLES ±		APPLICATION SPEC 114-137061					
MATERIAL - -	FINISH - -	WEIGHT -	SIZE A3	CAGE CODE 00779	DRAWING NO C-T2111082101100		
CUSTOMER DRAWING					SCALE 3:2	SHEET 1 OF 1	REV B

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[T2111082101-100](#)