








REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	INITIAL	14APR2015	DW	CW
	B	ECR-15-018270	09DEC2015	DW	CW
	B1	ECR-16-006849	13MAY2016	RL	CW
	C	ECR-21-111798	28SEP2021	WQR	CW

- NOTES:
1. TECHNICAL CHARACTERISTICS:
INSULATION MATERIAL: PC
RATED VOLTAGE: 250V
RATED CURRENT: 10A
INSULATION RESISTANCE: $\geq 400M\Omega$
RATED IMPULSE VOLTAGE: 4KV
POLLUTION DEGREE: 3
FLAMMABILITY: UL94V-0
MATING CYCLES: 500 CYCLES
OPERATION TEMPERATURE: $-40\sim+125^{\circ}C$
WIRE RANGE: 0.14~2.5 mm² (26~14 AWG)
CONTACT TYPE: CRIMP CONTACT
 2. CONTACT NEED TO BE ORDERED SEPARATELY.
(ORDER No. REFER TO DRAWING: T20200X10XX000)

- 注释:
1. 技术参数:
绝缘材料: PC
额定电压: 250V
额定电流: 10A
绝缘电阻: $\geq 400M\Omega$
额定脉冲电压: 4KV
污染等级: 3
阻燃等级: UL94V-0
插拔次数: 500次
工作温度: $-40\sim+125^{\circ}C$
接线范围: 0.14~2.5 mm² (26~14 AWG)
接线类型: 冷压接
 2. 端子需要单独订购.
(订货号参考图面: T20200X10XX000)

T2111122101-001	HMN-012-M WITHOUT LOGO HMN-012模块公插 不带LOGO, 产品型号和认证标示
T2111122101-000	HMN-012-M WITH LOGO HMN-012模块公插
PART NUMBER 料号	PART DESCRIPTION 描述

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN	14APR2015	TE Connectivity		
		CHK	14APR2015			
		APVD	14APR2015			
		PRODUCT SPEC	108-137121			
		APPLICATION SPEC	114-137121	NAME HMN-012-M		
		WEIGHT	-	SIZE	CAGE CODE	DRAWING NO
		Customer Drawing			A300779	©-T2111122101000
					SCALE	1:1
					SHEET	1 OF 1
					REV	C



T2111122101-001 SHOWN, ALL DIMENSIONS ARE SAME AS T2111122101-000, EXCEPT WITHOUT LOGO, TYPE DESCRIPTION, TUV AND CUL MARK
不带 LOGO, 产品型号和认证标示

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[T2111122101-000](#)