





REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	INITIAL	14NOV2016	BS	CW
	B	ECR-18-003111	23MAY2018	BS	CW



NOTES:

1. TECHNICAL CHARACTERISTICS:
INSULATION MATERIAL: PA
RATED VOLTAGE: 2000V
RATED CURRENT: 350A
RATED IMPULSE VOLTAGE: 12KV
POLLUTION DEGREE: 3
FLAMMABILITY: UL94V-0
WIRE RANGE: 35-120 mm²
CONTACT TYPE: CRIMP CONTACT

2. CONTACT NEED TO BE ORDERED SEPARATELY.
(ORDER No. REFER TO DRAWING:T2193502XXX000)




注释:

1. 技术参数:
绝缘材料: PA
额定电压: 2000V
额定电流: 350A
额定脉冲电压: 12KV
污染等级: 3
阻燃等级: UL94V-0
接线范围: 35-120 mm²
接线类型: 冷压接

2. 端子需要单独订购.
(订货号参考图面: T2193502XXX000)

T2193503201-000	HCM350-FC	HCM350 FEMALE INSERT, CRIMP HCM350母插、冷压型
PART NUMBER 零件料号	PART DESCRIPTION 零件描述	

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN BELL SU	14NOV2016	TE Connectivity			
DIMENSIONS: mm	TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC±- 1 PLC±- 2 PLC±- 3 PLC±- 4 PLC±- ANGLES±-	CHK KYLE ZENG	14NOV2016	NAME HCM350-FC			
		APVD CHRIS WANG	14NOV2016				
		PRODUCT SPEC		SIZE			
		APPLICATION SPEC		CAGE CODE		DRAWING NO	
MATERIAL		FINISH		WEIGHT		RESTRICTED TO	
-		-		-		-	
-		-		A3		C-T2193503201000	
CUSTOMER DRAWING				SCALE		SHEET	
				1:1		1 OF 1	
						REV B	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[T2193503201-000](#)