

P	LTR	DESCRIPTION	DATE	DWN	APVD
	A1	NEW DRAWING	01.04.2020	SI	SI

TAMPER-PROOF LABELS OVERVIEW


SERIES	PART NO.	DESCRIPTION	MATERIAL	TTDS
MV	D91458-000	MV-381191-5-8A	SV7000, Polyester silver (0,077 mm), Acrylic adhesive with „VOID“ Pattern	TTDS-084
TN	E48361-000	TN-381191-5-8A	PE7021, Polyethylene destructive white matt (0,07 mm), Acrylic adhesive	TTDS-091

Quantity per roll: 5.000 PCs

Labels across: 2

Winding: outside

length of roll: 60,6 m



approx.
Ø
136-139
[5.355-5.473]

Color-appearance
on roll



LABEL BUILD DETAILS		TOLERANCES mm [INCH]		THIS DRAWING IS A CONTROLLED DOCUMENT		DWN S. Iser / 01.04.2020		DATE		TE Connectivity							
	SUBSTRATE	LABEL HEIGHT: ±0,3 [.012]		DIMENSIONS mm [INCHES]  TOLERANCES UNLESS OTHERWISE SPECIFIED 0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± - 4 PLC ± - ANGLES ± -		CHK S. Iser / 01.04.2020		DATE <td colspan="2" rowspan="5">  Name Tamper-proof Label Size „381191" </td>		 Name Tamper-proof Label Size „381191"							
		LABEL WIDTH: ±0,3 [.012]				APVD S. Iser / 01.04.2020		DATE									
	ADHESIVE	WEB WIDTH: ±0,8 [.031]				PRODUCT SPEC		DATE									
		VERTICAL REPEAT: ±0,8 [.031]*				APPLICATION SPEC		DATE									
	LINER	HORIZONTAL REPEAT: ±0,8 [.031]*				WEIGHT MV: 0,073 g TN: 0,0059 g		SIZE				CAGE CODE		DRAWING NO		RESTRICTED TO	
		PRINT POSITIONING: ±0,8 [.031]*															
		LEFT MARGIN: ±0,4 [.016]															
		QUANTITY: -0% +2%															
		*NON ACCUMULATING															
				MATERIAL		FINISH				A3		C2290		C-TAMPER-PROOF			
				SEE TABLE													

All dimensions in mm [inch]
labels are centered on the liner
as long as not declared separately

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[E48361-000](#)