

| P | LTR | DESCRIPTION | DATE       | DWN | APVD |
|---|-----|-------------|------------|-----|------|
|   | A1  | NEW DRAWING | 01.04.2020 | SI  | SI   |

TAMPER-PROOF LABELS OVERVIEW


| SERIES | PART NO.   | DESCRIPTION    | MATERIAL                                                                  | TTDS     |
|--------|------------|----------------|---------------------------------------------------------------------------|----------|
| MV     | D91458-000 | MV-381191-5-8A | SV7000, Polyester silver (0,077 mm), Acrylic adhesive with „VOID“ Pattern | TTDS-084 |
| TN     | E48361-000 | TN-381191-5-8A | PE7021, Polyethylene destructive white matt (0,07 mm), Acrylic adhesive   | TTDS-091 |

Quantity per roll: 5.000 PCs

Labels across: 2

Winding: outside

length of roll: 60,6 m



approx.  
Ø  
136-139  
[5.355-5.473]

Color-appearance  
on roll



| LABEL BUILD DETAILS |           | TOLERANCES mm [INCH]            |  | THIS DRAWING IS A CONTROLLED DOCUMENT                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                          |  | DWN S. Iser / 01.04.2020 |  | DATE             |  | TE Connectivity |  |
|---------------------|-----------|---------------------------------|--|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|--|--------------------------|--|------------------|--|-----------------|--|
| <div></div>         | SUBSTRATE | LABEL HEIGHT: ±0,3 [.012]       |  | <div><div>DIMENSIONS mm [INCHES]</div><div></div><div>TOLERANCES UNLESS OTHERWISE SPECIFIED</div><div>0 PLC ± -</div><div>1 PLC ± -</div><div>2 PLC ± -</div><div>3 PLC ± -</div><div>4 PLC ± -</div><div>ANGLES ± -</div></div> <div><div>DWN S. Iser / 01.04.2020</div><div>CHK S. Iser / 01.04.2020</div><div>APVD S. Iser / 01.04.2020</div><div>PRODUCT SPEC</div><div>APPLICATION SPEC</div><div>WEIGHT MV: 0,073 g   TN: 0,0059 g</div></div> <div><div>NAME</div><div>TAMPER-PROOF LABEL SIZE „381191“</div></div> <div><div>SIZE A3</div><div>CAGE CODE C2290</div><div>DRAWING NO C-TAMPER-PROOF</div><div>RESTRICTED TO</div></div> |  |                          |  |                  |  |                 |  |
| <div></div>         | ADHESIVE  | LABEL WIDTH: ±0,3 [.012]        |  |                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                |  |                          |  |                  |  |                 |  |
| <div></div>         | LINER     | WEB WIDTH: ±0,8 [.031]          |  |                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                |  |                          |  |                  |  |                 |  |
|                     |           | VERTICAL REPEAT: ±0,8 [.031]*   |  |                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                |  |                          |  |                  |  |                 |  |
|                     |           | HORIZONTAL REPEAT: ±0,8 [.031]* |  |                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                |  |                          |  |                  |  |                 |  |
|                     |           | PRINT POSITIONING: ±0,8 [.031]* |  |                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                |  |                          |  |                  |  |                 |  |
|                     |           | LEFT MARGIN: ±0,4 [.016]        |  |                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                |  |                          |  |                  |  |                 |  |
|                     |           | QUANTITY: -0% +2%               |  |                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                |  |                          |  |                  |  |                 |  |
|                     |           | *NON ACCUMULATING               |  |                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                |  |                          |  |                  |  |                 |  |
| MATERIAL SEE TABLE  |           |                                 |  |                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                |  | FINISH                   |  | CUSTOMER DRAWING |  |                 |  |
|                     |           |                                 |  |                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                |  |                          |  | SHEET 1 of 1     |  |                 |  |
|                     |           |                                 |  |                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                |  |                          |  | REV A1           |  |                 |  |

All dimensions in mm [inch]  
labels are centered on the liner  
as long as not declared separately

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[D91458-000](#)