



# NECTOR T SPLICE CONNECTOR

TE Connectivity (TE)'s NECTOR T splice portfolio includes IP67/IP68 rated field installable connectors with standard M3 screw termination. NECTOR T splice connectors offer a new solution to high humidity and harsh environment installations like horticultural and outdoor lighting. It is an easy-to install and time saving alternative to traditional hard-wired electrical connections.

## BENEFITS

- Improves installation efficiency with easy to use screw termination
- Suited to broad range of wire sizes (1.5mm<sup>2</sup> to 4.0mm<sup>2</sup>)
- IP67/68 rated for moisture tight application
- Easy maintenance

## APPLICATIONS

- Horticultural and greenhouse lighting
- Garden lighting
- Outdoor displays
- Parking & garage lighting
- Stadium lighting
- Outdoor electrical installations

# NECTOR T SPLICE CONNECTOR

## ELECTRICAL

- Number of poles: 3
- IP rating: IP67/68
- Current rating: 25A max
- Voltage rating: 250V
- Operating temperature: 40°C to +85°C

## MECHANICAL

- Cable size OD: 7.0mm to 14mm
- Cable cross section area: 1.5mm<sup>2</sup> to 4.0mm<sup>2</sup>

## MATERIALS

- Mold material:
  - In-line splice and panel mount splice: UV protected PA66 V0 F1 rated
  - T splitter and 1 to 3 splitter: PA6 V2
- Contact/terminal material: Nickel plated brass
- Seal material: Silicone

## STANDARDS AND SPECIFICATIONS

- Application specifications: [114-133122](#)
- Production specifications: [108-133122](#)
- CE certification

## PRODUCT INFORMATION

Description	Part Number
NECTOR T 3 Position Wire-to-Wire Splice	<a href="#">2330191-1</a>
NECTOR T 3 Position Panel Mount Splice	<a href="#">2330192-1</a>
NECTOR T 3 Position T-Splitter	<a href="#">2330196-1</a>
NECTOR T Moisture Blocking Plug	<a href="#">2361045-1</a>



## te.com

© 2021 TE Connectivity. All Rights Reserved.

NECTOR, TE Connectivity, TE connectivity (logo) and Every Connection Counts are trademarks. All other logos, products and/or company names referred to herein might be trademarks of their respective owners.

While TE has made every reasonable effort to ensure the accuracy of the information in this brochure, TE does not guarantee that it is error-free, nor does TE make any other representation, warranty or guarantee that the information is accurate, correct, reliable or current. TE reserves the right to make any adjustments to the information contained herein at any time without notice. TE expressly disclaims all implied warranties regarding the information contained herein, including, but not limited to, any implied warranties of merchantability or fitness for a particular purpose. The dimensions in this catalog are for reference purposes only and are subject to change without notice. Specifications are subject to change without notice. Consult TE for the latest dimensions and design specifications.

9-1773984-7 03/21 JN

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[2330191-1](#) [2330192-1](#) [2330196-1](#) [2361045-1](#)